



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **N750 750 Cu Split Bolt** *Nsi Industries*

Catalog Number	N750
Manufacturer	Nsi Industries
Description	Copper Split Bolt Connector 750 MCM Copper Split Bolt Connectors Are High-Strength Solderless Service Connectors Made Of High-Copper Alloy For Copper and Copperweld Wires. Type For Two Maximum Wire Sizes.
Weight per unit	1.6 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 - 750 MCM
Wire Type	Class A & B

### **Material, Color, and Finish**

Color	Copper
Finish	COPPER
Housing Material	Copper

### **Dimensions and Weight**

Size	L=3.750 - W=2.130
------	-------------------

### **Descriptions**

Description	750 CU SPLIT BOLT
extra long description	NSI N-750 Split Bolt Copper 750
Features	Copper Split Bolt Connector 750 MCM Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.
Long Description	Copper Split Bolt Connector 750 MCM Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.
Product Type	Split Bolt Copper 750
Special Features	350-750 MCM - 2 Pack

### **Manufacturer Information**

Brand	Nsi Industries
GTIN	00662381020123
Manufacturers Part Number	N-750
UPC	662381020123



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Type ..... Copper Split Bolts .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 1.55 .....

## Uses, Certifications, and Standards

Application ..... Wire Termination .....

environmental conditions ..... 90 C .....

standard ..... UL486B .....