

72" Eight Blade Ceiling Fan

 Ceiling mounted • Damp location listed **PROGRESS LED**

Description:

Enjoy spending a comfortable evening in your favorite large living area as you are kept cool by a beautiful and expansive Vast ceiling fan. A refreshing airflow cascades down from the fan's Black blades that are complemented by the handsome Black finish. A subtle, white opal shade encloses a cutting-edge LED light source that emanates soft, welcoming light as the day's rays begin to fade, helping you to extend your evening in comfort for as long as you desire.

Specifications:

- Black (-31) (painted)
- Steel Construction
- Frosted Glass bowl
- Eight expansive Black blades generate a cooling airflow as they are complemented by a handsome Black finish
- A subtle, white opal shade encloses a cutting-edge LED light source that provides soft, welcoming light along with energy- and cost-saving benefits
- Performs best in your favorite large living areas, such as a great room, living room, or covered outdoor space where the fan's beautiful blades can keep you cool and comfortable
- Effortlessly control the full range dimming and fan speed capabilities with a six-speed, full function remote control with its batteries included, making it ready for immediate use
- The light kit contains a frosted, white opal glass shade and is comprised of an 18w dimmable, 3000k LED module that offers a 1400 lumens source, 90+ CRI
- Measures 72 in dia, 16-3/4 in ht, and 80 in lead wires
- Includes a 3/4 in X 6 in down rod with the option to order longer accessory rods separately
- UL damp location listed
- Can be used to comply with California Title 20 or to comply with 2016 Title 24 JA8
- Mounting hardware and a limited lifetime warranty are included
- Dimmable to 10% brightness
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 80" of wire supplied
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1400/77.7 (LM-82)
CCT	3000 K
CRI	90+ CRI
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-10 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Damp location listed Meets California Title 24 JA8-2016

P2550-3130K

Images:



Dimensions:

Diameter: 72"
Length: 72"
Height: 16-3/4"

Glass
Width: 7-1/8
Height: 7-7/8

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$15

\$3
|
\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
• Your cost depends on rates and use
• Energy Use: 29 Watts

All estimates based on typical use, excluding lights

Airflow

7982

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
• Airflow Efficiency: 273 Cubic Feet Per Minute Per Watt

ftc.gov/energy