



SKU: PB4-600-2N

UPC: 0783669179774

Features & Benefits:

Description: Aluminum Panelboard Lug, Dual Rated, Conductor Range 600-2, 4 Ports, 2 Holes, 1/2in Bolt Size, 1-3/4in Hole Spacing, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Contains DE-OX®	No
Mounting Hole Type	Thru
Number of Conductors	4
Number of Mounting Holes	2
Number of Poles	1
Number of Ports / Wireways	4
Wire Orientation	Perpendicular

Dimensions

Dimension G (IN)	0.625
Dimension G (mm)	15.875
Drive Size Main	1/2
Drive Type Main	Internal Hex
Height (IN)	3
Height BX (IN)	3.125
Length (IN)	5.687
Mounting Bolt/Stud Size (mm)	304.8
Mounting Hole Diameter (IN)	0.563
Mounting Hole Diameter (mm)	14.3002
Mounting Hole Spacing (IN)	1.75
Mounting Hole Spacing (mm)	44.45
Tang Length (IN)	3.125
Tang Length (mm)	79.375
Tang Thickness (IN)	0.75
Tang Thickness (mm)	19.05
Tang Width (IN)	2.469
Tang Width (mm)	62.7126
Weight (LB)	2.202
Weight BX (LB)	2.3356
Width (IN)	2.469
Width BX (IN)	3.875

Material and Finish

Conductor Material	Aluminum
Connector Finish	Tin
Insulation	NA

Material	Aluminum
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

Bolt and Screw Sizes

Mounting Bolt/Stud Size	1/2
Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	15/16
Wire Binding Torque	500

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 1
Direct Burial	No
Dual Rated	Yes
NEMA Code	S-588-3
UPC Code	78366917977

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
ROHS Indicator	RES
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
-------	--------

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	600 kcmil - 2 Str
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	600 kcmil - 2 Str
Conductor Range CU Stranded (Secondary, tap, load)	NA
Conductor Range AL Solid (Primary, run, main, line)	NA

Voltage

Voltage Rating

35 kV