



SKU: PBTD-3-750

UPC: 0783669078688

Features & Benefits:

Description: Nimbus Insulated Aluminum Multi-Tap Connector, Conductor Range 750-250, 3 Ports, Dual Sided Entry, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Contains DE-OX®	Yes
Number of Conductors	3
Number of Poles	1
Number of Ports / Wireways	3
Number of Usable Ports	3
Number of Usable Taps	3
Replacement Part(s)	PORTPLUG-1/0, SCREWCAP-1/0

Dimensions

Drive Size Main	1/2
Drive Type Main	Internal Hex
Height (IN)	3.206
Height BX (IN)	3.75
Height (mm)	81.4324
Length (IN)	4.87
Length (mm)	123.698
Max Insulation OD (IN)	1.202
Max Insulation OD (mm)	30.5308
Weight (LB)	1.539
Weight BX (LB)	4.9326
Width (IN)	3.405
Width BX (IN)	6.375
Width (mm)	86.487

Material and Finish

Conductor Material	Aluminum
Connector Finish	Tin
Insulation Material	Plastisol
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	15/16
Wire Binding Torque	500

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 3
Dual Rated	Yes
NEMA Code	S-588-4
UPC Code	78366907868

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	750 kcmil - 250 kcmil
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	750 kcmil - 250 kcmil
Conductor Range CU Stranded (Secondary, tap, load)	NA
Conductor Range AL Solid (Primary, run, main, line)	NA
Flex Conductor Range	NA

Voltage

Voltage Rating	600 V
----------------	-------

Color

Cap Color Main	Black
Cap Color Tap	Black
Color	Black

Environment and Temperature

Environmental Conditions	Cold temperature rated to -45°C
Flammability Rating	Insulation rated per UL 94
Temperature Rating	90°C