

# Eaton QBH1020GF

Catalog Number: QBH1020GF

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,20A,22kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB

## General specifications



Photo is representative

Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBH1020GF

UPC

786680222450

Product Length/Depth

3.5 in

Product Height

1.3 in

Product Width

6 in

Product Weight

0.47 lb

Warranty

1 year

Compliances

Contact Manufacturer

Certifications

UL 489

## Physical Attributes

### Circuit breaker type

QB

### Connection

Bolt-on

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#14-4 AWG

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

Bolt-on mounting

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBH1020GF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton QBH1020GF

Catalog Number: QBH1020GF

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,20A,22kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB

## General specifications



Photo is representative

Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBH1020GF

UPC

786680222450

Product Length/Depth

3.5 in

Product Height

1.3 in

Product Width

6 in

Product Weight

0.47 lb

Warranty

1 year

Compliances

Contact Manufacturer

Certifications

UL 489

## Physical Attributes

### Circuit breaker type

QB

### Connection

Bolt-on

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#14-4 AWG

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

Bolt-on mounting

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBH1020GF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)