



PENE4, Oxide Inhibitor, 4 Ounce Squeeze Bottle

By Burndy
Catalog # [PENE4](#)

Electrical sealing compound, Squeeze Bottle.



Application

For Copper To Copper

General

Application - For Use On	Copper to Copper
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	E
UPC	781810593141
UPC 12 Digit	7818105931411
Viscosity at 100 Fahrenheit	250 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	4 oz
Minimum Pack Quantity	1

Product Assets

- [3D Models - PENE4_MODEL-PDF](#)
- [3D Models - PENE4_MODEL-IGES](#)
- [3D Models - PENE4_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - sc087708-01](#)
- [SDS - PENETROX_E_Polish_GHS](#)
- [SDS - PENETROX_E_ESPANOL_GHS](#)
- [SDS - PENETROX_E_FRENCH_GHS](#)
- [SDS - PENETROX_E_RUSSIAN_GHS](#)
- [SDS - PENETROX_E_GHS](#)
- [SDS - PENETROX_E_GERMAN_GHS](#)
- [SDS - PENETROX_E_PORTUGUESE_GHS](#)



A proud member of the Hubbell Family.