


DESCRIPTION

The Lumark QZ Wedge is a compact, economical alternative to traditional floodlighting. The black or white finishes provide lasting durability with optics that deliver optimum beam control. U.L. listed and labeled for wet locations. CSA certified.

DIMENSIONS



QZ WEDGE

300 - 500 W
Quartz

FLOODLIGHT

ORDERING INFORMATION

SAMPLE NUMBER: QZ5L

Lamp Type Q=Quartz	Fixture Z=Wedge	Lamp Wattage 3=300W 5=500W	Lamp L=Lamp Included	Options & Accessories (See Below)
-----------------------	--------------------	----------------------------------	----------------------------	--------------------------------------

Options (add as suffix)
WHT=White

Accessories (order separately)
NKS-BZ=2" Slipfitter, Bronze
NKS-WHT=2" Slipfitter, White

- Die-cast aluminum housing finished in black or white paint for lasting durability
- Adjustable stem mounting arm fits 1/2" NPS outlet box cover
- Anodized aluminum reflector provides maximum beam control and efficiency
- Porcelain lamp sockets for 300-500W quartz lamp
- Heat- and weather-resistant gasketing seals out external contaminants
- Hinged door frame has toolless entry latch
- U.L. listed for wet locations. CSA certified
- Approximate net weight: 3 lbs. (1 kgs.)

NOTES: 1 Standard unit has 1/2" NPT threaded knuckle for mounting. 2" slipfitter is available as an accessory. 2 120 Volt operation only. 3 For complete product data, reference the Lumark Specification binder. 4 Specifications and dimensions subject to change without notice. 5 Products also available in non-US voltages and frequencies for international markets. 6 Consult your Cooper Lighting Representative for availability and ordering information.