

Project: _____ Type: _____ Prepared By: _____ Date: _____



Features and Benefits

- Replaces CFL 18W, 26W, and 32W G24q Lamps
- Ballast Compatible. Directly Compatible with Most Existing CFL Ballasts.
- Compatible with G24q / GX24q (4-pin CFL) installations
- 50,000 hour Lifespan
- Environmentally friendly, no mercury used
- UL Listed, DLC Listed
- Rated for use in enclosed and open fixtures in dry or damp locations
- 5 Year No Compromise Warranty
- Compatible with RAB specified 0-10V dimming system

Technical Specifications		
Performance	L70 Lifespan:	Other
Product Type: Compact	50,000 Hours	Equivalency: 26W Fluorescent
Input Wattage: 9W	Dimmable: Yes	Warranty (Years): RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty .
Typical Lumen Output: 1000	Construction	Electrical
Efficacy: 111 lm/W	Bulb Shape: PLC	Power Factor: Ballast Dependent
Color Temperature: 4000K Cool White	Finish: Frosted	Operating Temperature: -20°C - 45°C
CRI: 82	Base Type: G24q	Input Voltage: Ballast Dependent
	For Use Outdoors in Open Fixtures: No	

Technical Specifications (continued)

Electrical

Operating Frequency:

Ballast Dependent

Installation

Installation Type:

Type A, Plug and Play

Installation Orientation:

Vertical

Electrical Characteristics

THDi:

<20%

Compliance

UL Listed:

Yes

DLC Model Number:

PLC-9-V-840-DIR

CEC Status:

Lawful for sale in California

Application:

Suitable for damp locations and totally enclosed fixtures.

DLC Listed:


This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities. Designed to meet DLC 5.1 requirements.

DLC Product Code: PLUMZOCT7NLW

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	8.1	6.1	5.1
PALLET	3456	47.2	39.4	47.6

Wiring Diagram



Dimension

