PASS & SEYMOUR®
radiant® 15W USB
Charging Receptacles 15A, 125V



Conveniently power mobile devices quickly and reliably without the need for bulky AC adapters.

R26USBAC6, R26USBCC6


Charge phones, tablets and more with USB Outlets from the radiant® Collection. With 15W of power supplying the included USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, this USB updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Combination AC USB receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Posted side-wire terminal screws and external back-wire pressure plates for faster termination.

Available with (1) USB Type-A & (1) USB Type-C port or (2) USB Type-C ports to charge the latest mobile devices.



R26USBAC6LA

Type-A and Type-C ports carry minimum rating of 10,000 insertions.

AC USB receptacles are tamper-resistant to meet NEC. Patented shutter system — now with black "invisi-shutters" for an invisible effect preferred by end users — helps prevent improper insertion of foreign objects.

Slim design allows for installation in standard-depth wall boxes.

- **15W of charging capacity** with smart currentsharing technology to allow for full 3A through a singular Type-C port.
- **AC USB receptacles available in 15A, 125V.**
- **Back and side wire termination options** accommodate #14 AWG – #10 AWG stranded and solid copper wire.
- **Multiple color options available.**

3rd Party Compliance

cULus listed, UL listed. Complies with test requirements UL 498, UL 1310
CSA C22.2 No. 42, CSA c22.2 No. 223


Technical Information

Performance


Electrical	
Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Maximum Temperature Rise	30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current
No-Load Power Draw	10.7 mW Meets Department of Energy (DoE) Level VI requirement
FCC Part 15	Class B
Mechanical	
Terminal Accommodation	Back and side wire termination options accommodate #14 AWG - #10 AWG stranded and solid copper wire.
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact
RoHS	Compliant

Materials

Face	Polycarbonate
Back Body	Nylon
Line Contacts	CDA 260 Brass
Mounting Strap	.049" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate for Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel



R26USBAC6I



R26USBCC6I

Warranty

1 Year

Ordering Information

15W USB Type AC Chargers with Duplex Tamper-Resistant Receptacles

	Rating			Charging Capacity		3rd Party Compliance		
Catalog Number	A	V	Color	Wattage	Amperage/ Output	UL498 UL1310		C22.2 No. 42 C22.2 No. 223
R26USBAC6BK	15	125	Black	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBAC6DBCCV4	15	125	Dark Bronze	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBAC6I	15	125	Ivory	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBAC6LA	15	125	Light Almond	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBAC6NICC6	15	125	Nickel	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBAC6W	15	125	White	15W (per port)	6A, 5V Output	▪	▪	▪

15W USB Type CC Chargers with Duplex Tamper-Resistant Receptacles

	Rating			Charging Capacity		3rd Party Compliance		
Catalog Number	A	V	Color	Wattage	Amperage/ Output	UL498 UL1310		C22.2 No. 42 C22.2 No. 223
R26USBCC6BK	15	125	Black	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBCC6DBCCV4	15	125	Dark Bronze	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBCC6I	15	125	Ivory	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBCC6LA	15	125	Light Almond	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBCC6NICCV6	15	125	Nickel	15W (per port)	6A, 5V Output	▪	▪	▪
R26USBCC6W	15	125	White	15W (per port)	6A, 5V Output	▪	▪	▪



NEMA 5-15R

Vertical Markets

- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection...

- **GFCI Receptacles**
- **Standard & Tamper-Resistant Receptacles**
- **Paddle Switches**
- **Lighting & Fan Controls**
- **Timers**
- **Combination Devices**
- **Adjustable Night Lights**
- **Screwless Wall Plates**
- **Sensors**
- **Home Automation Controls**
- **Wireless Qi & USB charging receptacles**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street West
Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

FOLLOW US

CS3482 — October 2026 — For latest specs visit www.legrand.us/radiant

© Copyright 2026 Legrand All Rights Reserved