

Eaton REN-60

Catalog Number: REN-60

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name

Eaton Bussmann series REN fuse

Catalog Number

REN-60

UPC

051712100601

Product Length/Depth

0.82 in

Product Height

3 in

Product Width

3 in

Product Weight

1.4 lb

Warranty

Not Applicable

Compliances

Not Applicable

Electrical rating

Amperage Rating

60 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[REN-60~SUPER LAG RENEWABLE FUSE 60/250](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-60](#)

Eaton REN-60

Catalog Number: REN-60

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name

Eaton Bussmann series REN fuse

Catalog Number

REN-60

UPC

051712100601

Product Length/Depth

0.82 in

Product Height

3 in

Product Width

3 in

Product Weight

1.4 lb

Warranty

Not Applicable

Compliances

Not Applicable

Electrical rating

Amperage Rating

60 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[REN-60~SUPER LAG RENEWABLE FUSE 60/250](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-60](#)