



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC3RED 20A 120/277VAC B+S Wire 3W SW RD

Pass & Seymour/LeGrand

Catalog Number	PS20AC3RED
Manufacturer	Pass & Seymour/LeGrand
Description	3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2240 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	TP
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, Universal, Fluorescent, LED, Halogen, Xenon, CFL
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	277 VAC, 120 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	20A 120/277VAC B+S WIRE 3W SW RD
extra long description	P&S PS20AC3RED 20A 120/277VAC B+S W
Features	Chemical Resistant
Long Description	3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire 3W SW Red
Special Features	Heavy duty switch, back & side wire, with lock



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195439
Manufacturers Part Number	PS20AC3-RED
UPC	785007195439

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.224

Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL CULUS, UL20, FEDSPEC