



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RF9617AW Z-Wave Plus Accessory Switch

*Eaton Wiring Devices*

Catalog Number	RF9617AW
Manufacturer	Eaton Wiring Devices
Description	Eaton Z-Wave Plus Accessory Switch, Accessory Switch, 120V, Wiring Leads, Push Button, Alpine White, Three-Way, 32°F to 104°F (0°C to 40°C), Three-Way, Polycarbonate, RF9601
Weight per unit	0.0010 (lbs/each)
Product Category	Lighting Controls

### Features

dimensions	1.3800 IN X 1.8000 IN X 3.8100 IN
media	Yes
Voltage Rating	120 V

### Descriptions

Description	Z-WAVE PLUS ACCESSORY SWITCH
extra long description	EWD RF9617AW Eaton Z-Wave plus acce
Features	Eaton's complete offering of wireless lighting controls are easy to install, require no special wiring and are perfect for both new construction and existing homes. With our Z-Wave Plus wireless collection you get enhanced cybersecurity, improved wireless performance and flexibility to choose from 10 different colors to match your lighting mood and room decor.
Long Description	Eaton Z-Wave plus accessory switch, Accessory switch, 120V, Wiring leads, Push button, Alpine white, Three-way, 32°F to 104°F (0°C to 40°C), Three-way, Polycarbonate, RF9601
Product Type	Eaton Z-Wave Plus Accessory Switch
Special Features	RF Controls Accessories

### Manufacturer Information

Brand	Eaton
GTIN	00032664755224
Manufacturers Part Number	RF9617AW
UPC	032664755224

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Accessory switch

### Packaging

Carton	1
Package	6
Weight Per each	0.001



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Operating Temperature	32 to 104 °F (0 to 40 °C)
standard	cULus Listed,FCC Compliant