



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street  
74701-0000, OK Durant  
Phone: 580-745-5448  
Fax: 580-745-5449



## PS20AC4RED 20A 120/277VAC B+S Wire 4W SW RD

*Pass & Seymour/Legrand*

Catalog Number	PS20AC4RED
Manufacturer	Pass & Seymour/Legrand
Description	4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2260 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Halogen, LED, CFL, Universal, Incandescent, Fluorescent, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	4
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE 4W SW RD
extra long description	P&S PS20AC4RED 20A 120/277VAC B+S W
Features	Chemical Resistant
Long Description	4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire 4W SW Red
Special Features	High strength toggle, heavy duty toggle bumpers, locking support



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street  
74701-0000, OK Durant  
Phone: 580-745-5448  
Fax: 580-745-5449

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007195507
Manufacturers Part Number	PS20AC4-RED
UPC	785007195507

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.226

## Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL UL, CULUS, CSA, UL 20, FEDSPEC