



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Andrew Dr  
30281-0000, GA Stockbridge  
Phone: 470-440-4222  
Fax: 678-369-9160



## RTTP6010 7/8" Tip Bit

L.H. Dottie CO.

Catalog Number	RTTP6010
Manufacturer	L.H. Dottie CO.
Description	Tip Bit, 5 Drill Stages, 9/16 In. Minimum Drill Diameter, 7/8 In. Maximum Drill Diameter, M2 High Speed Steel Material, Cobalt Titanium Coated Finish, 7/8 In. Size, 1/4 In. Shank Diameter, Hex Shank Type
Weight per unit	0.4500 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Material	M2 High Speed Steel
shaft diameter	1/4
Shank Diameter	1/4
Shank Type	HEX

### Material, Color, and Finish

Finish	Cobalt Titanium Coated
--------	------------------------

### Dimensions and Weight

Size	7/8
------	-----

### Descriptions

Description	7/8" TIP BIT
extra long description	DOTTIE RTTP6010 7/8" Base & 1 Tip -
Long Description	Tip Bit, 5 drill stages, 9/16 in. minimum drill diameter, 7/8 in. maximum drill diameter, M2 High Speed Steel material, Cobalt Titanium Coated finish, 7/8 in. Size, 1/4 in. shank diameter, Hex shank type
Product Type	7/8" Base & 1 Tip - Tip Bits
Special Features	Features: Tri-Cut Tip Cuts Smoother, Faster And Cooler, "Plier Tite" Tip Fit

### Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002812111
Manufacturers Part Number	RTTP6010
UPC	781002812111

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Tip Bit



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Andrew Dr  
30281-0000, GA Stockbridge  
Phone: 470-440-4222  
Fax: 678-369-9160

## Packaging

Carton	1
Weight Per each	0.45