

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



S11A Nylon-Ins Butted Seam STD Closed Connector *Minnesota Mining (3M)*

3000	
Catalog Number	S11A
Manufacturer	Minnesota Mining (3M)
Description	3M™ Scotchlok™ Color-Coded Closed-End Connector Is An
	Electrical Crimp Sleeve Connector With A Copper Insert That
	Allows For Fast Splicing Of Copper Conductors. The
	Vinyl-Insulated Connector Is 600V-Rated For Building Wire and
	1000V-Rated For Signs, Fixtures or Luminaires. It Withstands
	Temperatures Of -40 to 221 Degrees F (-40 to 105 Degrees C).
Weight per unit	1.3 (lbs/each)
Product Category	Large Terminals & Connectors
Descriptions	
Description	NYLON-INS BUTTED SEAM STD CLOSED CONNECTOR
extra long description	3M 7000133427 3M™ Scotchlok™ Closed
Features	3M™ Scotchlok™ Closed-End Connector is color-coded for quick
	and easy identification of the wire size required. It allows for
	quick wire insertion with a smooth, flared entry. The copper
	insert offers good conductivity. RoHS 2011/65/EU Compliant.
Long Description	3M™ Scotchlok™ Color-Coded Closed-End Connector is an
	electrical crimp sleeve connector with a copper insert that allows
	for fast splicing of copper conductors. The vinyl-insulated
	connector is 600V-rated for building wire and 1000V-rated for
	signs, fixtures or luminaires. It withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C).
Product Type	3M™ Scotchlok™ Closed-End Connectors
Manufacturer Information	O.M. GOOGO IIO. GOOGO EIIG GOIII GOOGO
Brand	Scotchlok
GTIN	00051128589977
Manufacturers Part Number	S11A
UPC	051128589977
Taxonomies, Classifications, and (Categories
Category Description	WIDE NUTS
Туре	Closed End
Packaging	
Carton	100
Weight Per each	1.282