



S1240C 12" 40LB Natural Stronghold CBL Tie

Panduit Corporation

Catalog Number	S1240C
Manufacturer	Panduit Corporation
Description	The S12-40-C Stronghold Cable Ties Offers Contractors An Economical Cable Tie Option For Commercial Construction and General-Purpose Applications. Intermediate, 11.81" (300MM) Length, Made Of Nylon 6.6, AH-2 Plenum Rated, Are Natural In Color and Come In Packages Of 100.
Weight per unit	0.2990 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	40

Dimensions and Weight

Length	11.8
Thickness	0.05
Width	NA

Descriptions

Description	12" 40LB NATURAL STRONGHOLD CBL TIE
extra long description	PAN S12-40-C StrongHold™ S12-40-C C
Long Description	The S12-40-C StrongHold Cable Ties offers contractors an economical cable tie option for commercial construction and general-purpose applications. Intermediate, 11.81" (300mm) length, made of Nylon 6.6, AH-2 Plenum rated, are natural in color and come in packages of 100.

Product Type	Stronghold™ S12-40-C Cable Tie, Natural, Pa 6.6, 40LB Min Lo
Special Features	Plenum

Manufacturer Information

Brand	Panduit®
GTIN	00613056257955
Manufacturers Part Number	S12-40-C
UPC	613056257955

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Availability

minimum qty	100
-------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5500 Wheeler Avenue
72901-0000, AR Fort Smith
Phone: 479-648-1902
Fax: 479-648-1960

Packaging

Carton	100
Package	1000
Weight Per each	0.299

Uses, Certifications, and Standards

standard	UL 62275 Compliant (Type 2, 21), RoHS Compliant
----------	---