



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353



PV1038RXL Pan-Term® PV10-38RX-L Loo *Panduit Corporation*

Catalog Number	PV1038RXL
Manufacturer	Panduit Corporation
Description	Ring Terminal, 12 – 10 Awg, 3/8" Stud Size, Vinyl Insulated, Expanded Insulation For Large Wire O.D., Standard Package.
Weight per unit	0.3150 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Expanded Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	3/8"
------	------

Descriptions

Description	PAN-TERM® PV10-38RX-L LOO
extra long description	PAN PV10-38RX-L Pan-Term® PV10-38RX
Long Description	Ring Terminal, 12 – 10 AWG, 3/8" stud size, vinyl insulated, expanded insulation for large wire O.D., standard package.
Product Type	Pan-Term® PV10-38RX-L Loose Piece Ring Terminal

Manufacturer Information

Brand	Panduit®
GTIN	00074983801787
Manufacturers Part Number	PV10-38RX-L
UPC	074983801787

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Packaging

Carton	50
Package	500
Weight Per each	0.315



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353

Uses, Certifications, and Standards

Enclosure	Ring shape
Mounting	5/16
standard	UL Listed 587H E52164, CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)