



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV2510CT00 2-1/2IN PVC Coated Rigid

Calpipe Industries, Inc

Catalog Number	PV2510CT00
Manufacturer	Calpipe Industries, Inc
Description	Rigid Conduit, Steel Material; Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; 10 Foot; 2.489 Inch Inner Diameter; 2.955 Inch Outer Diameter; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard
Weight per unit	N/A
Product Category	20220415171915

Features

Applicable Standard	ANSI C80.1, NEMA RN-1
End Style	Threaded
Material	Steel
Wall Thickness	0.193 INCH

Material, Color, and Finish

Finish	Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior
--------	--

Dimensions and Weight

Inner Diameter	2.489 INCH
Length	10 Foot
Outer Diameter	2.955 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Constructional Feature Corrosion Resistant; Includes Coupling; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mill
Commodity Description	Pvc Schedule 40 Conduit
Description	2-1/2IN PVC COATED RIGID
extra long description	STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 10 FOOT; 2.489 INCH INNER DIAMETER; 2.955 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 593 POUND PER 100 FOOT WEIGHT; 170 FOOT PER BUNDLE STANDARD PACKAGE; 2-1/2 INCH TRADE SIZE; 0.193 INCH WALL THICKNESS; THREADED END STYLE; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; INCLUDES COUPLING; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRAN
Long Description	RIGID CONDUIT, STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 10 FOOT; 2.489 INCH INNER DIAMETER; 2.955 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD
Product Type	Rigid Conduit

Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656077259
Manufacturers Part Number	PV2510CT00
Model	PV
UPC	847656077259

Trade Size

Trade Size	2-1/2 INCH
------------	------------

Packaging

Carton	1
Standard Package	170 Foot per Bundle
Weight	593 Pound per 100 Foot
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 6, CUL
----------	-----------