


PART NUMBER	SIZE	"R"	"□"	"H"	"S" MIN	"B" MIN	"L"
5133823	½"	4"	4"	4"	1 ½"	N/A	6 ¼"
5133824	¾"	4 ½"	4 ½"	4 ½"	1 ½"	N/A	7 ⅛"
5133825	1"	5 ¾"	5 ¾"	5 ¾"	1 ⅞"	N/A	9"
5133826	1 ¼"	7 ¼"	7 ¼"	7 ¼"	2"	N/A	11 ⅜"
5133827	1 ½"	8 ¼"	8 ¼"	8 ¼"	2"	N/A	13"
5133828	2"	9 ½"	9 ½"	9 ½"	2"	N/A	15"
5133829	2 ½"	10 ½"	10 ½"	10 ½"	3"	N/A	16 ½"
5133830	3"	13"	13"	13"	3 ⅛"	N/A	20 ⅜"
5133831	3 ½"	15"	15"	15"	3 ¼"	N/A	23 ½"
5133832	4"	16"	16"	16"	3 ⅜"	N/A	25 ⅛"
5133835	5"	24"	24"	24"	3 ⅝"	N/A	37 ⅝"
5133834	6"	30"	30"	30"	3 ¾"	N/A	47 ⅛"
5133993D	8"	48"	48"	48"	6 ⅝"	N/A	75 ⅜"



ETL LISTED
 CONFORMS TO UL651
 ETL CONTROL #3107144
 Meets NEMA TC3
 See NEC Article 352 for use
 Material is Rigid PVC
 Bend Tolerance is $\pm 2^\circ$



CANTEX
 INC.
 Fort Worth, TEXAS

90° Elbows Plain End
 Schedule 40 Standard Radius Elbows

Drawn By: CD Branch Date: 4/30/26 Ref.