

# Specifications



Photo is representative

## Eaton PVML-7-UNV34

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 130 lm/W, Die cast aluminum, No mounting module, Type V, 347-480 Vac, 57W

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
<b>CATALOG NUMBER</b>	PVML-7-UNV34
<b>UPC</b>	662276906143
<b>PRODUCT LENGTH/DEPTH</b>	13 in
<b>PRODUCT HEIGHT</b>	13.13 in
<b>PRODUCT WIDTH</b>	12.75 in
<b>PRODUCT WEIGHT</b>	20.8 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC IEC
<b>NEMA RATING</b>	4X
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

## Product specifications

<b>LUMENS</b>	7000
<b>LUMENS PER WATT</b>	130
<b>COLOR TEMPERATURE</b>	Cool white
<b>MOUNTING METHOD</b>	No mounting module
<b>OPTICAL DISTRIBUTION</b>	Type V
<b>GUARD TYPE</b>	No guard
<b>VOLTAGE RATING</b>	347-480 Vac
<b>FREQUENCY RATING</b>	50/60 Hz
<b>WATTAGE</b>	57W
<b>DIMMING</b>	Dimmable driver
<b>POWER FACTOR</b>	> 0.90
<b>EQUIVALENT LUMINAIRE</b>	175W HID
<b>MATERIAL</b>	Die cast aluminum
<b>LENS MATERIAL</b>	Heat and impact resistant glass

## Resources

3D MODELS	<a href="#">SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures</a>
BROCHURES	<a href="#">Crouse-Hinds series DLC approved lighting products</a> <a href="#">Crouse-Hinds series Global LED lighting portfolio</a> <a href="#">Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure</a> <a href="#">Crouse-Hinds series industrial LED lighting solutions</a>
CATALOGS	<a href="#">Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page</a>
CERTIFICATION REPORTS	<a href="#">EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires</a> <a href="#">Champ Pro PVML Industrial LED Light Fixtures UL certification</a> <a href="#">Champ Pro PVML Industrial LED Light Fixtures Canadian certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 1882 - Champ VMVL and PVML LED luminaires</a> <a href="#">IF 1888 - Champ VMVL and PVML Driver Replacement</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - PVML-7-UNV34</a> <a href="#">Champ Pro PVM Industrial LED</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



Photo is representative

## Eaton PVML-7-UNV34

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 130 lm/W, Die cast aluminum, No mounting module, Type V, 347-480 Vac, 57W

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
<b>CATALOG NUMBER</b>	PVML-7-UNV34
<b>UPC</b>	662276906143
<b>PRODUCT LENGTH/DEPTH</b>	13 in
<b>PRODUCT HEIGHT</b>	13.13 in
<b>PRODUCT WIDTH</b>	12.75 in
<b>PRODUCT WEIGHT</b>	20.8 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC IEC
<b>NEMA RATING</b>	4X
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

## Product specifications

<b>LUMENS</b>	7000
<b>LUMENS PER WATT</b>	130
<b>COLOR TEMPERATURE</b>	Cool white
<b>MOUNTING METHOD</b>	No mounting module
<b>OPTICAL DISTRIBUTION</b>	Type V
<b>GUARD TYPE</b>	No guard
<b>VOLTAGE RATING</b>	347-480 Vac
<b>FREQUENCY RATING</b>	50/60 Hz
<b>WATTAGE</b>	57W
<b>DIMMING</b>	Dimmable driver
<b>POWER FACTOR</b>	> 0.90
<b>EQUIVALENT LUMINAIRE</b>	175W HID
<b>MATERIAL</b>	Die cast aluminum
<b>LENS MATERIAL</b>	Heat and impact resistant glass

## Resources

3D MODELS	<a href="#">SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures</a>
BROCHURES	<a href="#">Crouse-Hinds series DLC approved lighting products</a> <a href="#">Crouse-Hinds series Global LED lighting portfolio</a> <a href="#">Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure</a> <a href="#">Crouse-Hinds series industrial LED lighting solutions</a>
CATALOGS	<a href="#">Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page</a>
CERTIFICATION REPORTS	<a href="#">EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires</a> <a href="#">Champ Pro PVML Industrial LED Light Fixtures UL certification</a> <a href="#">Champ Pro PVML Industrial LED Light Fixtures Canadian certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 1882 - Champ VMVL and PVML LED luminaires</a> <a href="#">IF 1888 - Champ VMVL and PVML Driver Replacement</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - PVML-7-UNV34</a> <a href="#">Champ Pro PVM Industrial LED</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.

