
Carlon^{*}



IMPORTANT:

- THE USE OF DUCT SPACERS FOR DIRECT BURIAL MAY RESULT IN EXCESSIVE POINT DEFLECTIONS UNLESS PROPER DESIGN ENGINEERING IS APPLIED, SUCH AS THE PROPER COMPACTION OF THE APPROPRIATE BACKFILL MATERIAL.
- CARLON® IS NOT RESPONSIBLE FOR SNAP-LOC® SPACERS USED IN DIRECT BURY APPLICATIONS... DESIGN ENGINEERS AND CONTRACTORS ARE RESPONSIBLE FOR THE DESIGN OF THE INSTALLATION.

NOTES:

- I. MATERIAL: HIGH IMPACT STYRENE.
- 2. USE CARLON $^{\circledR}$ QUICK-SET CEMENT GLUE DURING ASSEMBLY OR SPOT GLUE AFTER ASSEMBLY TO SECURE.
- 3. PROLONGED EXPOSURE TO DIRECT SUNLIGHT COULD CAUSE MATERIAL BRITTLENESS.
- 4. NONMETALLIC SNAP-LOC® SPACERS ARE DESIGNED SPECIFICALLY FOR USE WITH NONMETALLIC DUCT, WITH A MAXIMUM O.D. DIMENSIONS OF NEMA TC-2, TC-6, TC-8 AND ASTM F512.

| GENERAL NOTES | | | _ | L | |
|---|----------------------------------|-----------|----------|-------------|--|
| I. ALL DIMENSIONS ARE FOR REFERENCE ONLY. | | | | homas@Betts | |
| 2. DIMENSIONS IN BRACKETS [] | | | | www.tnb.com | |
| ARE IN METRIC UNITS. | DESCRIPTION: CDAC | 'ED IN | TEDMED | NATE | |
| REVISIONS | SPACER - INTERMEDIATE | | | | |
| C SEE ERN (2012853) | | | | | |
| FOR APPROVAL SIGNATURES | ORIGINAL PROJECT NO / (ERN NO) | SHEET NO: | REV. NO: | DRAWING NO: | |
| & RELEASE DATE. PROJECT NO: 5AM000013 | ND55840 / (2009708) | 1 OF 2 | С | WSD-AC03237 | |

| 00000 111 | 8 X 2 | 10.755 | 4.378 | 10.64 |
|-----------|----------------|------------------|---------|---------|
| S289SJN | (203.2 x 50.8) | (273.2) | (111.2) | (270.3) |
| S289SHN | 8 X I-1/2 | 10.255 | 4.378 | 10.14 |
| | (203.2 X 38.1) | (260.5) | (111.2) | (257.6) |
| S289RLN | 6 X 3 | 9.750 | 3.375 | 9.64 |
| | (152.4 X 76.2) | (247.7) | (85.8) | (244.9) |
| S289RJN | 6 X 2 | 8.750 | 3.375 | 8.64 |
| | (152.4 X 50.8) | (222.3) | (85.8) | (219.5) |
| S289RHN | 6 X 1-1/2 | 8.250 | 3.375 | 8.14 |
| | (152.4 X 38.1) | (209.6) | (85.8) | (206.8) |
| S289PLN | 5 X 3 | 8.690 | 2.845 | 8.57 |
| | (127.0 X 72.6) | (220.7) | (72.3) | (216.7) |
| S289PJN | 5 X 2 | 7.690 | 2.845 | 7.57 |
| | (127.0 X 50.8) | (195.3) | (72.3) | (192.3) |
| S289PHN | 5 X 1-1/2 | 7.190 | 2.845 | 7.07 |
| | (127.0 X 38.1) | (182.6) | (72.3) | (179.6) |
| S289NLN | 4 X 3 | 7.625 | 2.312 | 7.51 |
| | (101.6 X 76.2) | (193.7) | (58.7) | (190.6) |
| S289NJN | 4 X 2 | 6.625 | 2.312 | 6.51 |
| | (101.6 X 50.8) | (168.3) | (58.7) | (165.4) |
| S289NHN | 4 X 1-1/2 | 6.125 | 2.312 | 6.01 |
| | (101.6 X 38.1) | (155.6) | (58.7) | (152.7) |
| S289NFN | 4 X I | 5.609 | 2.312 | 5.73 |
| | (101.6 X 25.4) | (142.5) | (58.7) | (145.5) |
| S289LLN | 3 X 3 | 6.625 | 1.812 | 6.51 |
| | (76.2 X 76.2) | (168.3) | (46.0) | (165.4) |
| S289LJN | 3 X 2 | 5.625 | 1.812 | 5.51 |
| | (76.2 X 50.8) | (142.9) | (46.0) | (140.0) |
| S289LHN | 3 X 1-1/2 | 5.125 | 1.812 | 5.01 |
| | (76.2 X 38.1) | (130.2) | (46.0) | (127.3) |
| S289JLN | 2 X 3 | 5.500 | 1.250 | 5.38 |
| | (50.8 X 76.2) | (1 39 .7) | (31.8) | (136.7) |
| S289JJN | 2 X 2 | 4.500 | 1.250 | 4.38 |
| | (50.8 X 50.8) | (114.3) | (31.8) | (111.3) |
| S289JHN | 2 X 1-1/2 | 4.000 | 1.250 | 3.88 |
| | (50.8 X 38.1) | (101.6) | (31.8) | (98.6) |
| PART NO. | DESCRIPTION | DIM 'A' | DIM 'B' | DIM 'C' |

| GENERAL NOTES | | | - | 1 | | | |
|---|----------------------------------|-----------|----------|-------------|--|--|--|
| I. ALL DIMENSIONS ARE FOR REFERENCE ONLY. | | | | homas@Betts | | | |
| 2. DIMENSIONS IN BRACKETS [] | www.tnb.com | | | | | | |
| ARE IN METRIC UNITS. | SPACER - INTERMEDIATE | | | | | | |
| REVISIONS | | | | | | | |
| C SEE ERN (2012853) | | | | | | | |
| FOR APPROVAL SIGNATURES | ORIGINAL PROJECT NO / (ERN NO) | SHEET NO: | REV. NO: | DRAWING NO: | | | |
| & RELEASE DATE. PROJECT NO: 5AM000013 | ND55840 / (2009708) | 2 OF 2 | С | WSD-AC03237 | | | |