

Project Name

Location

Prepared By



SATCO S29390

18W/LED/HID/5000K/100-277V E26

Notes

(www) 08-02-2023 00:44:11

General

| | |
|-------------------------|--|
| Status | Discontinued |
| Substitute | S49390 |
| Watts | 18W |
| Incandescent Equivalent | 120W |
| Fluorescent Equivalent | 32W |
| HID Equivalent | 70W |
| Volts | 120V-277V |
| Shape | Corncob |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Clear |
| CCT (Kelvin) | 5000K |
| Temperature | Natural Light |
| CRI | 80+ |
| Lumens | 2700L |
| Beam Spread | 300 |
| Dimmable | Non-Dimmable |
| Hours Rated | 50000 |
| Product Category | Corncob |
| Technology | LED |
| Min Compartment Size | Length: 8.5 in. Width: 6 in. Depth: 6 in. |
| Ballasting Requirements | Ballast Bypass- Direct wire only 100V-277V |

Electrical

| | |
|-----------------------|----------------------------|
| Working Voltage | AC 90-305V |
| Operating Frequency | 50/60Hz |
| Power Factor | >.9 |
| Operating Position | Universal |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

Physical

| | |
|--------------|-------|
| MOL | 6.78 |
| MOD | 2.75 |
| Lens Finish | Clear |
| Weight (lb.) | 0.86 |

Additional Information

| | |
|----------------------------|--|
| Additional Info | Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg) |
| Rated For Enclosed Fixture | Yes |
| IP Rating | IP65 |
| Installation Notes | Not for use in vapor tight fixtures. |
| Warranty | 5-Years |

Compliance

| | |
|----------------------|---|
| Safety Listing | cULus - Certified; cULus - Classified; cULus - Listed |
| Location Rating | Damp |
| DLC Approved | No |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| Colorado Status | Lawful for sale |
| Hawaii Status | Lawful for sale |
| Nevada Status | Lawful for sale |
| Vermont Status | Lawful for sale |
| Washington Status | Lawful for sale |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |