

QB1A

75 watt Quartz Bullet Flood with silicone O-ring gasket, thick tempered glass lens, internal and external cooling fins. Gold plated socket contacts and 250°C Teflon coated wires for extended lamp life. Lamp supplied.

Color: Bronze


Weight: 1.0 lbs

Lamp Info

Type: T-4
Watts: 75W
Shape/Size: N/A
Base: N/A
ANSI: N/A
Hours: 1,500
Lamp Lumens: 1,500
Efficacy: 20 LPW

Ballast Info

Type: N/A
120V: N/A
208V: N/A
240V: N/A
277V: N/A
Input Watts: 75W
Efficiency: 100%



Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

Lens Gasket:

High temperature silicone gasket stays in place during relamping.

Reflector:

Semi-specular anodized aluminum.

Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250° C socket wires.

Lens:

Thick, tempered glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Replacement Lamps:

.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.



QB1A

75 watt Quartz Bullet Flood with silicone O-ring gasket, thick tempered glass lens, internal and external cooling fins. Gold plated socket contacts and 250°C Teflon coated wires for extended lamp life. Lamp supplied.

Color: Bronze


Weight: 1.0 lbs

Lamp Info

Type: T-4
Watts: 75W
Shape/Size: N/A
Base: N/A
ANSI: N/A
Hours: 1,500
Lamp Lumens: 1,500
Efficacy: 20 LPW

Ballast Info

Type: N/A
120V: N/A
208V: N/A
240V: N/A
277V: N/A
Input Watts: 75W
Efficiency: 100%



Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

Lens Gasket:

High temperature silicone gasket stays in place during relamping.

Reflector:

Semi-specular anodized aluminum.

Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250° C socket wires.

Lens:

Thick, tempered glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Replacement Lamps:

.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

