



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279



S29891 4W CFC/Led/30K/CL/120V

Satco

| | |
|------------------|-------------------------------------|
| Catalog Number | S29891 |
| Manufacturer | Satco |
| Description | Satco S29891 4W CFC/Led/30K/CL/120V |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Led Decorative C, Ca, F, G Sha |

Features

| | |
|----------------|----------------|
| average life | 15000 |
| connection | Candelabra |
| Fixture Type | LED Filament |
| lumens | 350 |
| Shape | CA11 |
| Voltage Rating | 120 |
| Warranty | 3 Year Limited |
| Wattage | 4 |

Material, Color, and Finish

| | |
|-------|-----------|
| Color | Colorless |
|-------|-----------|

Dimensions and Weight

| | |
|------|----------------------|
| Size | MOL: 4.69, MOD: 1.38 |
|------|----------------------|

Descriptions

| | |
|------------------|---|
| Description | 4W CFC/LED/30K/CL/120V |
| Long Description | SATCO S29891 4W CFC/LED/30K/CL/120V |
| Product Type | 4W CFC/Led/30K/CL/120V |
| Special Features | CEC: Non-Compliant - Not 82 CRI ; Dimmable: Yes Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; 3000K color temperature ; 80 CRI ; 360 degree beam spread ; Enclosed lamp rated ; 3 Year Limited Warranty |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923298912 |
| Manufacturers Part Number | S29891 |
| sub brand | Satco |
| UPC | 045923298912 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED DECORATIVE C, CA, F, G SHAPE LAMPS |
| Type | LED |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Per each 0.02

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus damp location rated