



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



QBHW2060 2 Pole 60A QBHW BRKR

Eaton Corp

Catalog Number	QBHW2060
Manufacturer	Eaton Corp
Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-Pole, 60A, 22 Kaic, 120/240V, Bolt-On
Weight per unit	0.7000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 2.3000 IN X 4.8000 IN
interrupt rating	22
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	2 POLE 60A QBHW BRKR
extra long description	ETN QBHW2060 2 Pole 60 Amp QBHW Bre
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 60A, 22 kaIC, 120/240V, Bolt-on
Product Type	2 Pole 60 Amp QBHW Breaker

Manufacturer Information

Brand	Eaton
GTIN	00786679392904
Manufacturers Part Number	QBHW2060
UPC	786679392904

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	12
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Uses, Certifications, and Standards

Application

standard

Generation - Renewable Energy - Alternative Energy
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other Other Generation - Conventional Energy - Conventional
Energy Datacenters - IT Space: CI and Hyper Converged
UL Listed, CSA Certified