



REDUCING BUSHINGS AND ADAPTERS



R- 31



R- 65



ADUP-12

Class I, Div. 1 & 2, Groups A,B,C,D
Class I, Zone 1, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G

UL Standard: 1203
 CSA Standard: C22.2 No. 30

LISTED File No. E 10514

Certified File No. LR11716

FEATURES-SPECIFICATIONS

Application

- To reduce the trade size of a taped hole or hub.

Reducer Features

- Tapered threads (NPT)
- Smooth internal bushing protects conductors
- Threaded for Rigid Conduit or IMC

ADUP Features

- Tapered threads (NPT)
- Enlarged drilled and tapped hole openings by an NPT size

Material/Finish

Copper-free Aluminum

(less than 4/10 of 1%)
 (R-10 through R-109)

Natural Finish

Steel/Zinc Plated

(RE20S through RE109S)

For ATEX and IEC Ex certified Reducing Bushings and Adapters, contact factory or check the website

REDUCING BUSHINGS			
CATALOG NUMBER		HUB SIZE	DIMENSIONS
KILLARK ALUM.	STEEL		BODY LENGTH
R-10	—	1/2" — 3/8"	3/4"(19)
R-20	RE20S	3/4" — 3/8"	11/16"(18)
R-21	RE21S	3/4" — 1/2"	13/16"(21)
R-30	RE30S	1" — 3/8"	11/16"(18)
R-31	RE31S	1" — 1/2"	13/16"(21)
R-32	RE32S	1" — 3/4"	13/16"(21)
R-41	RE41S	1-1/4" — 1/2"	13/16"(21)
R-42	RE42S	1-1/4" — 3/4"	13/16"(21)
R-43	RE43S	1-1/4" — 1"	1"(25)
R-51	RE51S	1-1/2" — 1/2"	13/16"(21)
R-52	RE52S	1-1/2" — 3/4"	13/16"(21)
R-53	RE53S	1-1/2" — 1"	1"(25)
R-54	RE54S	1-1/2" — 1-1/4"	1-1/64"(28)
R-61	RE61S	2" — 1/2"	13/16"(21)
R-62	RE62S	2" — 3/4"	13/16"(21)
R-63	RE63S	2" — 1"	1"(25)
R-64	RE64S	2" — 1-1/4"	1/64"(28)
R-65	RE65S	2" — 1-1/2"	1/32"(31)
R-73	RE73S	2-1/2" — 1"	1"(25)
R-74	RE74S	2-1/2" — 1-1/4"	1" (25)
R-75	RE75S	2-1/2" — 1-1/2"	1"(25)
R-76	RE76S	2-1/2" — 2"	1"(25)
R-84	RE84S	3" — 1-1/4"	1" (25)
R-85	RE85S	3" — 1-1/2"	1-1/4"(32)
R-86	RE86S	3" — 2"	1-1/4"(32)
R-87	RE87S	3" — 2-1/2"	1-1/4"(32)
R-96	RE96S	3-1/2" — 2"	1-3/8"(35)
R-97	RE97S	3-1/2" — 2-1/2"	1-3/8"(35)
R-98	RE98S	3-1/2" — 3"	1-3/8"(35)
R-106	RE106S	4" — 2"	1-1/2"(38)
R-107	RE107S	4" — 2-1/2"	1-1/2"(38)
R-108	RE108S	4" — 3"	1-1/2"(38)
R-109	RE109S	4" — 3-1/2"	1-1/2"(38)

ADUP ADAPTERS

CATALOG NUMBER	DESCRIPTION	
ADUP-01	Male 3/8"	Female 1/2"
ADUP-12	Male 1/2"	Female 3/4"
ADUP-23	Male 3/4"	Female 1"

Material/Finish

Copper-free Aluminum

(less than 4/10 of 1%)

Natural Finish

MADE IN THE USA



REDUCING BUSHINGS AND ADAPTERS



R-31



R-65



ADUP-12

Class I, Div. 1 & 2, Groups A,B,C,D
Class I, Zone 1, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G

UL Standard: 1203
 CSA Standard: C22.2 No. 30

LISTED File No. E 10514

Certified File No. LR11716

FEATURES-SPECIFICATIONS

Application

- To reduce the trade size of a taped hole or hub.

Reducer Features

- Tapered threads (NPT)
- Smooth internal bushing protects conductors
- Threaded for Rigid Conduit or IMC

ADUP Features

- Tapered threads (NPT)
- Enlarged drilled and tapped hole openings by an NPT size

Material/Finish

Copper-free Aluminum

(less than 4/10 of 1%)
 (R-10 through R-109)

Natural Finish

Steel/Zinc Plated

(RE20S through RE109S)

For ATEX and IEC Ex certified Reducing Bushings and Adapters, contact factory or check the website

REDUCING BUSHINGS			
CATALOG NUMBER		HUB SIZE	DIMENSIONS
KILLARK ALUM.	STEEL		BODY LENGTH
R-10	—	1/2" — 3/8"	3/4"(19)
R-20	RE20S	3/4" — 3/8"	11/16"(18)
R-21	RE21S	3/4" — 1/2"	13/16"(21)
R-30	RE30S	1" — 3/8"	11/16"(18)
R-31	RE31S	1" — 1/2"	13/16"(21)
R-32	RE32S	1" — 3/4"	13/16"(21)
R-41	RE41S	1-1/4" — 1/2"	13/16"(21)
R-42	RE42S	1-1/4" — 3/4"	13/16"(21)
R-43	RE43S	1-1/4" — 1"	1"(25)
R-51	RE51S	1-1/2" — 1/2"	13/16"(21)
R-52	RE52S	1-1/2" — 3/4"	13/16"(21)
R-53	RE53S	1-1/2" — 1"	1"(25)
R-54	RE54S	1-1/2" — 1-1/4"	1-1/64"(28)
R-61	RE61S	2" — 1/2"	13/16"(21)
R-62	RE62S	2" — 3/4"	13/16"(21)
R-63	RE63S	2" — 1"	1"(25)
R-64	RE64S	2" — 1-1/4"	1/64"(28)
R-65	RE65S	2" — 1-1/2"	1/32"(31)
R-73	RE73S	2-1/2" — 1"	1"(25)
R-74	RE74S	2-1/2" — 1-1/4"	1" (25)
R-75	RE75S	2-1/2" — 1-1/2"	1"(25)
R-76	RE76S	2-1/2" — 2"	1"(25)
R-84	RE84S	3" — 1-1/4"	1" (25)
R-85	RE85S	3" — 1-1/2"	1-1/4"(32)
R-86	RE86S	3" — 2"	1-1/4"(32)
R-87	RE87S	3" — 2-1/2"	1-1/4"(32)
R-96	RE96S	3-1/2" — 2"	1-3/8"(35)
R-97	RE97S	3-1/2" — 2-1/2"	1-3/8"(35)
R-98	RE98S	3-1/2" — 3"	1-3/8"(35)
R-106	RE106S	4" — 2"	1-1/2"(38)
R-107	RE107S	4" — 2-1/2"	1-1/2"(38)
R-108	RE108S	4" — 3"	1-1/2"(38)
R-109	RE109S	4" — 3-1/2"	1-1/2"(38)

ADUP ADAPTERS

CATALOG NUMBER	DESCRIPTION	
ADUP-01	Male 3/8"	Female 1/2"
ADUP-12	Male 1/2"	Female 3/4"
ADUP-23	Male 3/4"	Female 1"

Material/Finish

Copper-free Aluminum

(less than 4/10 of 1%)

Natural Finish

MADE IN THE USA