

FEATURES & SPECIFICATIONS

INTENDED USE — SBL LED wraparound provides a digital lighting platform to deliver general ambient lighting for surface-mount applications. The SBL provides a similar look to that of an existing fluorescent wrap with all of the excellent benefits of LED: energy savings, long life, and maintenance savings. Ideal for closets, storage rooms, and offices.

CONSTRUCTION - Linear side prisms control brightness, pyramidal bottom prisms minimize lamp immore properties and properties are properties as the properties of the propage. Continuous side flanges on fixture body provide light trap and continuous diffuser support to prevent accidental opening and simplify maintenance. Full depth, white enamel end plates.

Die-formed from code gauge cold-rolled steel. Channel cover snaps into place without the use of tools. Full end cap factory installed to reduce job site labor.

OPTICS — The translucent white diffuser reduces glare and pixilation without impacting performance.

ELECTRICAL — Long-life LEDs, coupled with high-efficiency drivers, provide superior quantity and quality of illumination for extended service life. 90% LED lumen maintenance at 50,000 hours (L90/50,000). The LEDs have a CRI of 82

eldoLED driver options deliver choice of dimming range and choices for control, while assuring flicker-free, low-current inrush, 89% efficiency and low EMI.

Pair the SBL with the fixture mount Sensor Switch LSXR sensor for additional energy savings when the space is unoccupied. The LSXRHL sensor dims the fixture down to a low-level setting when there is no occupancy. This option is ideal for stairwells, back rooms, and closets due to the low occupancy level in those spaces.

Optional nLight® embedded controls continuously monitor system performance, allow for constant lumen management / compensation function, facilitate simple "plug-and-play" network and controls upgrading via Cat-5 cable. Ballast disconnect provided where required to comply with US and Canadian codes.

LISTINGS — CSA certified to meet U.S. and Canadian standards...

Damp listed.

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.

BUY AMERICAN ACT — Product with the BAA option is assembled in the USA and meets the Buy America(n) government procurement requirements under FAR, DFARS and DOT regulations. Please refer to www. acuitybrands.com/buy-american for additional information.

WARRANTY — 5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Catalog Number	
Notes	
Туре	

Square-basket LED Wraparound













****** Capable Luminaire

This item is an A+ capable luminaire, which has been designed and tested to provide consistent color appearance and out-of-the-box control compatibility with simple commissioning.

- All configurations of this luminaire meet the Acuity Brands' specification for chromatic consistency
- This luminaire is part of an A+ Certified solution for nLight® control networks when ordered with drivers marked by a shaded background*
- This luminaire is part of an A+ Certified solution for nLight control networks, providing advanced control functionality at the luminaire level, when selection includes driver and control options marked by a shaded background*

To learn more about A+, visit www.acuitybrands.com/aplus.

*See ordering tree for details

DECORATIVE RESIDENTIAL SBI 2



ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: SBL2 2000LM 80CRI 35K MIN10 GZT MVOLT

SBL2													
Series		Lumens ¹		CRI		Colort	emperature	Minimur	n Dimming Level	Dimming	l	Voltage	
SBL2	2' LED wrap	2000LM	2000 lumens	80CRI	80 CRI	30K 35K 40K 50K	3000 K 3500 K 4000 K 5000 K	MIN10 MIN1 NODIM SLD	Dims to 10% ² Dims to 1% ³ On/off, non-dimming ⁴ Step-level dimming ⁴	(blank) GZT ZT	none 10 Generic 0-10V Dimming eldoLED 0-10 Dimming	MVOLT 347	120-277V 347V ^{5,11}

Emergency Option	Control Input/Lumen Management Options 10	Occupancy Control Options	Occupancy Sensor Technology Option	Options
EMG For use with nLight on generator supply EM power ⁶	NLIGHT nLight enabled CL80 NLIGHT nLight enabled, constant lumen output, 80%	LSXRHL Sensor Switch® fixture mount sensor with High/ Low occupancy operation ^{7,8} LSXR10 Sensor Switch® fixture mount sensor with on/off occupancy operation ⁷	PIR Passive Infrared ¹²	BAA Buy America(n) Act Compliant BDP Factory Installed Ballast Disconnect Plug

ORDERING INFORMATION

Catalog number	UPC	Description	Description Lumens		Voltage	Wattage	Pallet qty	Standard carton qty.	
SBL2 LP835 9	190887819458	2' LED Wraparound	1,937	3500 K	120-277	17	140	1	
SBL2 LP840 ⁹	190887819489	2' LED Wraparound	1,967	4000 K	120-277	17	140	1	

Notes

- Approximate lumen output. Requires GZT control option.
- Requires GZT, ZT, or NLIGHT control.
- Not available with Control or Sensor Options.
 Not available with SLD option.
- nLight EMG option requires a conection to existing nLight network. Power is provided from a separate N80 or N100 enabled fixture. Requires NLIGHT.
- 7 Requires MIN1, ZT and PIR options.
- 8 Dims to approximately 10% light output when unoccupied.
- 9 Product in stock.
- 10 When Control Input/ Lumen Management option $specified\ leave\ Dimming\ section\ blank.$
- 11 347 not available with battery option
- 12 Only available with Occupancy Control option.

Performance Data										
Lumen Package	Lumens	Input Watts	LPW							
2000LM 80CRI 30K	1894	16.9	112							
2000LM 80CRI 35K	1937	16.9	115							
2000LM 80CRI 40K	1967	16.9	116							
2000LM 80CRI 50K	2039	16.9	121							



	Sensor Switch LSXRHL Sensor					
oe:	10 - Low Mount 360° coverage					

Lens type Dimming: **HL** - High/Low Occupancy operation


Min Dim Level: 3V - approximately 10% light output when unoccupied

Time Delay: 5M - 5 minutes



PHOTOMETRICS

SBL2 2000LM 80CRI 35K



Coefficients of Utilization

		000	,,,,,	,,,,,	,, 0,	IIIZat	.011						
pf				2	20%								
рс		80%			70%			50%		Zon	ial Lumei	n Summa	ry
pw	70%	50%	30%	50%	30%	10%	50%	30%	10%	Zone	Lumens	% Lamp	% Fixture
0	117	117	117	114	114	114	107	107	107	0° - 30°	484	25.0	25.0
1	106	101	96	98	94	90	92	89	86	0° - 40°	781	40.3	40.3
2	96	87	80	85	78	73	80	75	70	0° - 60°	1348	69.6	69.6
3	88	77	68	75	67	61	70	64	59	0° - 90°	1795	92.7	92.7
د 4	80	68	59	66	58	51	63	55	50	90° - 120°	94	4.9	4.9
25	74	61	52	59	51	44	56	49	43	90° - 130°	114	5.9	5.9
^ட 6	68	55	46	53	45	39	51	43	38	90° - 150°	136	7.0	7.0
7	63	50	41	48	40	34	46	39	33	90° - 180°	141	7.3	7.3
8	59	45	37	44	36	31	42	35	30	0° - 180°	1937	100.0	100.0
9	55	41	33	41	33	27	39	32	27				
10	51	38	30	38	30	25	36	29	24				

MOUNTING DATA

Suspension Kit Ceiling Types: F1 for use with most T-bar and screw slot grid ceiling applications. Designed for on-grid and off-grid installations.

F2 for use with recessed or surface-mount horizontal J-box applications.

For unit or row installation; surface or suspend mounting.


Individual installation — Two single-stem hangers required.

 $For aircraft \ cable, one \ STACG_, \ STACGF_, \ or \ STACGE_required \ for \ each \ suspension \ point.$

Note: 2' configurations with emergency option cannot be stem mounted.

See ACCESSORIES below for hanging devices.





DIMENSIONS

All dimensions are inches (centimeters) unless otherwise noted.

Specifications 2-5/8 (6.7) Length: 24 (61.0) Width: 8-5/8 (21.9) Depth: 2-5/8 (6.7) 8-5/8 (21.9)

All dimensions are inches (centimeters) unless otherwise indicated.