



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100
65803-0000, MO Springfield
Phone: 417-429-1665
Fax: 417-429-1666



SC15120S25L 14.96" 50LB Nat CBL Tie *Panduit Corporation*

Catalog Number	SC15120S25L
Manufacturer	Panduit Corporation
Description	The SC15-120-S25-L Stronghold Clamp Cable Ties Offers Contractors An Economical Clamp Cable Tie Option For Commercial Construction and General-Purpose Applications. The Cable Tie Design Allows You to Secure Cable Bundles to Another Surface, For Use With #1/4 (M6) Screw. Light-Heavy, 14.96" (380MM) Length, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 50.
Weight per unit	0.6860 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	14.96
Thickness	0.08
Width	NA

Descriptions

Description	14.96" 50LB NAT CBL TIE
extra long description	PAN SC15-120-S25-L StrongHold™ SC15
Long Description	The SC15-120-S25-L StrongHold Clamp Cable Ties offers contractors an economical clamp cable tie option for commercial construction and general-purpose applications. The cable tie design allows you to secure cable bundles to another surface, for use with #1/4 (M6) screw. Light-Heavy, 14.96" (380mm) length, made of Nylon 6.6, are natural in color and come in packages of 50.
Product Type	Stronghold™ SC15-120-S25-L Cable Tie, Natl, Pa 6.6, 50LB Min
Special Features	Indoor

Manufacturer Information

Brand	Panduit®
GTIN	00613056258341
Manufacturers Part Number	SC15-120-S25-L
UPC	613056258341

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100
65803-0000, MO Springfield
Phone: 417-429-1665
Fax: 417-429-1666

Availability

minimum qty 50

Packaging

Carton 50

Package 500

Weight Per each 0.686

Uses, Certifications, and Standards

standard UL 62275 Compliant (Type 2, 21), UL Listed #E56854, RoHS
Compliant