ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RF9601AW Z-Wave Plus Switch SP 15A 120V Alpine WH

Eaton Wiring Devices

Catalog Number	RF9601AW
Manufacturer	Eaton Wiring Devices
Description	Eaton Z-Wave Plus Decorator Switch, Power Failure Memory, 15A, 120V, Alpine White, 60 HZ, Led, CFL, Incandescent, MLV, Elv, Fluorescent, and Halogen, Single-Pole, Three-Way, Multi-Location, Used With RF9517
Weight per unit	0.0010 (lbs/each)
Product Category	Lighting Dimmers

Features

amperage rating	15A
dimensions	1.3800 IN X 1.8000 IN X 3.8100 IN
media	Yes
Voltage Rating	120 V

Descriptions

Description	Z-WAVE PLUS SWITCH SP 15A 120V ALPINE WH
extra long description	EWD RF9601AW Z-Wave Plus Switch SP
Features	Eaton's complete offering of wireless lighting controls are easy to install, require no special wiring and are perfect for both new construction and existing homes. With our Z-Wave Plus wireless collection you get enhanced cybersecurity, improved wireless performance and flexibility to choose from 10 different colors to match your lighting mood and room decor.
Long Description	Eaton Z-Wave plus decorator switch, Power Failure Memory, 15A, 120V, Alpine white, 60 Hz, LED, CFL, incandescent, MLV, ELV, fluorescent, and halogen, Single-pole, Three-way, Multi-location, Used with RF9517
Product Type	Z-Wave Plus Switch SP 15A 120V
Special Features	Power Failure Memory

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00032664755149
Manufacturers Part Number	RF9601AW
UPC	032664755149

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Decorator Switch

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.001

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Frequency Rating	60 Hz
Operating Temperature	32 to 104 °F (0 to 40 °C)
standard	NOM,cULus Listed,FCC Compliant