Project	C	Catalog #	Туре	
Prepared by	Ν	lotes	Date	




# 🖌 Interactive Menu

- Order Information page 2
- Photometric Data page 4
- Control Solutions page 4
- Connected Systems page 4
- Product Warranty

### **Top Product Features**

- Ultra-low profile surface luminaire with wide distribution
- · Ceiling or wall mounting in compatible junction boxes
- Retrofit 4" recessed downlights with screwbase adapter included
- 2700K, 3000K, 3500K, 4000K or 5000K color temperature; 90 CRI
- Dimmable with 120V dimmer

# **Dimensional and Mounting Details**





# HALO

# **SMD4 Series**

4" Round and Square

Typical Applications Residential

## **Product Certification**





Refer to ENERGY STAR® Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements Certified to California Appliance Efficiency Database under JA8.

### **Product Features**







# **HALO**

### **Order Information**

SAMPLE NUMBER: SMD4R6930WH=4" Round Surface Mount Downlight, 90CRI, 3000K

Junction Box Installation: Order junction box separately, as supplied by others, to complete installation.

Recessed Installation: Order Halo recessed housing separately to complete installation.

Models	Lumens	CRI / CCT	Finish	Accessories	Packaging
Models	Lumens	CRI / CCT	Finish	Accessories	Packaging
SMD4R = 4" Round Surface Mount Downlight, 120V SMD4S = 4" Square Surface Mount Downlight, 120V	6 = 600 lumen series	927 = 90CRI, 2700K 938 = 90CRI, 3000K 935 = 90CRI, 3500K 940 = 90CRI, 4000K 950 = 90CRI, 5000K	WH = Mate White	Designer Trims         SMD4RTRMSN = 4" Round SMD Satin Nickel         SMD4RTRMBZ = 4" Round SMD Tuscan Bronze         SMD4RTRMWH = 4" Round SMD White (paintable)         SMD4STRMSN = 4" Square SMD Satin Nickel         SMD4STRMSH = 4" Square SMD Satin Nickel         SMD4STRMWH = 4" Square SMD White (paintable)         T24HWKIT = Title 24 Cable harness kit used to convert incandescent and low voltage housings to LED         HE26LED = E26 Screw base adapter for retrofit (included)         Image: T24HWKIT	R = Recycled

\*For T20 California product, apply "-CA" to the catalog number (i.e. SMD4R6930WH-CA)

### Accessories

### **Designer Trims**



Housings			

# Compatible Halo LED Housings with LED luminaire connector (high-efficacy compliant)

Halo LED Housings H995ICAT = 4" IC, airtight shallow new construction housing, LED, 120 - 277V H995RICAT = 4" IC, airtight shallow remodeler housing, LED, 120 - 277V H245ICAT = 4" IC, airtight ultra-shallow new construction housing, LED, 120 - 277V H245RICAT = 4" IC, airtight ultra-shallow remodeler housing, LED, 120 - 277V

#### Housings

### Compatible Halo Incandescent E26 Screwbase Housings

 Halo Housings

 H99TAT = 4" non-IC, airtight shallow new construction housing, E26, 120V

 H99TAT = 4" non-IC, airtight shallow remodeler housing, E26, 120V

 H99ICAT = 4" non-IC, airtight shallow new construction housing, E26, 120V

 E4TATSB = 4" non-IC, airtight shallow new construction housing, E26, 120V

 E4TATSB = 4" non-IC, airtight shallow new construction housing, adjustable socket bracket, E26, 120V

 E4TATSB = 4" non-IC, airtight shallow remodeler housing, adjustable socket bracket, E26, 120V

 E4TATSB = 4" non-IC, airtight shallow remodeler housing, adjustable socket bracket, E26, 120V



# HALO

# SMD4R & SMD4S LED Series

## Compatible with Eaton's Crouse-Hinds Junction Boxes



**TP316** for non-metallic cable 4" x 4" x 2-1/8" (102mm x 102mm x 54mm)



**TP317** for metal clad cable 4" x 4" x 2-1/8" (102mm x 102mm x 54mm)

### • TP316 - for non-metallic cable

- TP317 for metal clad cable
- UL Listed
- · Refer to www.crouse-hinds.com

# **Compatible with Many OtherJunction Boxes\***



**4" octagon light fixture/fan steel box** 4" x 4" x 2-1/8" (102mm x 102mm x 54mm)



**4" round new work non-metallic light fixture/fan box** 4" diameter x 2-3/16" (102mm x 56mm)



**4" octagon steel box** 4" x 4" x 1-1/2" (102mm x 102mm x 38mm)



**3-1/2" round new work non-metallic ceiling box** 3-1/2" diameter x 2-3/4" (89mm x 70mm)



**4" square deep steel box** 4" x 4" x 2-1/8" (102mm x 102mm x 54mm)



**3-1/2" round old work non-metallic box** 4-1/4" O.D. flange, 3-1/2" I.D. x 2-5/8" (108mm O.D., 89mm I.D. x 67mm)



**4" square standard steel box** 4" x 4" x 1-1/2" (102mm x 102mm x 38mm)



**4" round surface mount box** 4" diameter x 1-1/2" (102mm x 38mm) Requires SLD4RAD adapter



**4**" round new work non-metallic box with hanger bar assembly 4" diameter x 2-3/16" (102mm x 56mm)

\*This is a representative list of compatible junction boxes only. Information contained in this literature about other manufacturers' products is from published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Cooper Lighting Solutions makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must determine that site conditions are suitable to allow proper installation of the mounting bracket in the box.



# HALO

# SMD4R & SMD4S LED Series

# **Product Specifications**

### Housing

- Non-electrically conductive polycarbonate frame.
  High impact diffuse polystyrene lens provides shielding to the light guide with no pixilation
- Stamped aluminum housing provides thermal cooling achieving L70 at 50,000 hours in IC and non-IC applications

### Gaskets

 Closed cell gasket achieves restrictive airflow and wet location requirements without additional caulking

#### **Optics**

 Precision acrylic light guide organizes source flux into wide distribution with 1.2 – 1.4 spacing criteria useful for general area illumination

#### LED

- Mid power led array provide a uniform source with high efficiency and long life
- Available in 90 CRI minimum, R9 greater than 50 and color accuracy within 3 SDCM provide color accuracy and uniformity

#### Driver

- Integral 120V 50/60Hz constant current driver provides noise free operation
- Continuous, flicker-free dimming from 100% to 5% with select leading or trailing edge 120V phase cut dimmers
- Dimming to 5% is best assured using dimmers with low end trim adjustment. Consult dimmer manufacturer for compatibility and conditions of use. (Note some dimmers require a neutral in the wallbox.)
- Inline electrical quick connect and E26 adapter (provided) provides mains connections.

### **Photometric Data**

SMD4R6927WH							
Luminair	e lumens	690					
Input	watts	9.5					
LER (	LPW)	73					
	0-180	1.26					
Spacing Criteria	90-270	1.26					
	Diagonal	1.38					
Beam angle	e (degrees)	112					
Field angle	162						
Max. C	243						
Zonal lumen	% Lumens						
0-30	187	27.2%					
0-40	44.5%						
0-60	78.6%						
0-90	690	100.00%					

### **Mounting/Retention**

- Adjustable spider plate allows for quick installation into both junction boxes and recessed housings
- Friction blades included

### **Electrical Junction Box Mounting**

- The SMD may be used in compatible electrical junction boxes in direct contact with insulation including spray foam insulation
- Suitable for installation in many 3-1/2" and 4" square, octagon, and round electrical junction boxes
- Installer must ensure compatibility of fit, wiring and proper mounting in the electrical junction box. This includes all applicable national and local electrical and building coded

### **Recessed Housing Mounting**

- May be installed in IC recessed housings in direct contact with insulation
   Note: Not for use in recessed housing in direct
- contact with spray foam insulation. Refer to NEMA LSD 57-2013

### Friction Blade 4"

- Precision formed friction blades included
- For retrofit in 4" nominal housings
- Friction blade design allows the SMD to be installed in any position within the housing aperture (360 degrees)

#### **Designer Skins (Sold Separately)**

- SMD skins are accessory rings in both round and square. These skins attach to the SMD for a permanent finish. Refer to the SMD accessories specification sheet for details.
  - Matte White (Paintable)
  - Satin Nickel
  - Tuscan Bronze

### Compliance

- cULus listed / certified for use with Halo housings, classified for use with other's housings, see instruction sheet for conditions of acceptability.
- Wet and Damp Location listed, airtight per ASTM-E283
- Suitable for use in closets, compliant with NFPA® 70, NEC® Section 410.16 (A)(3) and 410.16 (C)(5)
- EMI/RFI emissions per FCC 47CFR Part 15B
- · Contains no mercury or lead and RoHS compliant.
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy luminaire compliance, reference the California Energy Commission Title 20 Appliance Efficiency Database for current listings
- Can be used for International Energy Conservation Coe (IECC) and Washington State Energy Code high efficiency luminaire compliance

### Warranty

 Five year limited warranty, consult website for details. <u>www.cooperlighting.com/warranty</u>

### **Energy Data**

	Round Square			
Lumens (5000K models)	786	810		
Input Power	9.7 W         10 W           0.0811 A         0.0829 A           81 lm/W         81 lm/W			
Input Current				
Efficiency				
THD	13.3 13.2 120V			
Input Voltage				
Frequency	50/60 Hz 90 CRI 0.99			
CRI				
Power Factor				
T Ambient	-30	⊦40°C		
Sound Rating	Class A			



	SIMD430927WH							
Luminair	e lumens	750						
Input	watts	9.5						
LER (	LPW)	79						
	0-180	1.24						
Spacing Criteria	90-270	1.24						
	Diagonal	1.36						
Beam angle	e (degrees)	109						
Field angle	e (degrees)	162						
Max. Candela 278								
Zonal lumen	Zonal lumen Lumens % Lumens							
0-30	207	27.6%						
0-30 0-40	207 336	27.6% 44.9%						
	-							
0-40	336	44.9%						

SMD4S6927WH

# SMD4R & SMD4S LED Series


Cat. No.	CRI	сст	Lumens	Power (W)	LPW
SMD4R6927WH	93	2700	690	9.50	72.6
SMD4R6930WH	93	3000	700	9.70	72.2
SMD4R6935WH	94	3500	740	9.70	76.3
SMD4R6940WH	94	4000	760	9.80	77.6
SMD4R6950WH	91	5000	786	9.70	81.0
				1	
SMD4S6927WH	92	2700	750	9.50	78.9
SMD4S6930WH	92	3000	790	9.90	79.8
SMD4S6935WH	93	3500	740	9.90	74.7
SMD4S6940WH	93	4000	800	10.10	79.2
SMD4S6950WH	90	5000	810	10.00	81.0

		alues at Nadir ming Angle	
DD (FT)	SMD4R6927WH (FC)	SMD4S6927WH (FC)	DIA (FT)
5.5	8.0	9.2	16.3
7	5.0	5.7	20.9
8	3.8	4.3	23.8
9	3.0	3.4	26.8
10	2.4	2.8	29.7
12	1.7	1.9	35.7

DD = distance down to illuminated work plane

FC = initial foot-candles at nadir

DIA = diameter



		Multiplier T	able		
CCT Option	2700K	3000K	3500K	4000K	5000K
CCT Multipiler	1.00	1.014	1.042	1.083	1.083



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2023 Cooper Lighting Solutions All Rights Reserved. Specifications and dimensions subject to change without notice.

PS518032EN page 5 February 22, 2023 9:35 AM