



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East  
71360-0000, LA Pineville  
Phone: 318-767-0900  
Fax: 318-767-0010



## SN1632B1100 100A MB 16-32 Circuit *Siemens Industry Inc*

Catalog Number	SN1632B1100
Manufacturer	Siemens Industry Inc
Description	STD PNR LC MB 16S/32C 1PH 100A N1 Gry
Weight per unit	N/A
Product Category	Distribution Equipment

### Descriptions

Description	100A MB 16-32 CIRCUIT
extra long description	MAIN BREAKER TYPE; 15.5 INCH WIDTH X 4.46 INCH DEPTH X 22.13 INCH HEIGHT SIZE; 32 MAX. NUMBER OF CIRCUITS; 16 MAX. NUMBER OF SPACES; UL 50/67/486/489/869/943 APPROVAL; 120/240 VOLT AC VOLTAGE RATING; 22 KILOAMP INTERRUPTING RATING; 100 AMP CURRENT RATING; SURFACE/FLUSH COVER TYPE; INDOOR, NEMA 1 ENCLOSURE TYPE; 1-PHASE 3-WIRE CIRCUIT CONFIGURATION; BONDED NEUTRAL TYPE; BOTTOM FEED LOCATION; ALUMINUM BUS MATERIAL; PLUG-ON BREAKER MOUNTING; ENCLOSURE HEIGHT 21 INCH; TEMPERATURE RATING 60/75 DEG F; APPLICABLE
Long Description	STD PNR LC MB 16S/32C 1PH 100A N1 GRY
Product Type	Main Breaker Load Center

### Manufacturer Information

Brand	Siemens
GTIN	00804766703249
Manufacturers Part Number	SN1632B1100
UPC	804766703249

### Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
----------------------	----------------------

### Packaging

Carton	1
Weight Per each	0