Project	Catalog #	Туре	
Prepared by	Notes	Date	



# **HALO**

# RL56 | LED 600 Series

5"/6" LED Recessed Retrofit Module-Trim

**Typical Applications** 

Residential

# Interactive Menu

- Order Information page 2
- Product Specifications page 3
- Photometric Data page 4
- Energy & Performance Data page 4
- Product Warranty

# **Product Certification**













# **Product Features**




air 🕾




# **Top Product Features**

- ENERGY STAR® certified
- · 90 CRI: 2700K, 3000K, 3500K, 4000K, or 5000K CCT
- · Lumens: 600, 900, 1200
- · Retrofits existing 5 or 6" housings with screwbase adapter included"
- · Use with 5 and 6" LED housings new construction and remodel"

## **RL56 Dimensions**









HALO RL56 LED 600 Series

# **Order Information**

## SAMPLE ORDER NUMBER: RL560WH6927-RL56TRMWHB

Complete unit includes a RL56 Baffle-Trim LED Module and a 5" or 6" compatible housing, ordered separately. Optional accessory designer trim ring ordered separately.

#### RL56 600 Series

## Accessories (order separately)

RL56 600 Series	Accessories (order separately)
RL560WH6927= 5"/6" Retrofit Baffle - Trim LED Module, 90CRI, 2700K, Matte White RL560WH6930= 5"/6" Retrofit Baffle - Trim LED Module, 90CRI, 3000K, Matte White RL560WH6935= 5"/6" Retrofit Baffle - Trim LED Module, 90CRI, 3500K, Matte White RL560WH6940= 5"/6" Retrofit Baffle - Trim LED Module, 90CRI, 4000K, Matte White RL560WH6950= 5"/6" Retrofit Baffle - Trim LED Module, 90CRI, 5000K, Matte White	Designer Trims RL56TRMSNB= 5/6" Satin Nickel Trim Ring, Baffle RL56TRMTBZB= 5/6" Tuscan Bronze Trim Ring, Baffle RL56TRMWHB= 5/6" White Paintable Trim Ring, Baffle RL56TRMWHB= 5/6" Matte Black Trim Ring, Baffle RL56TRMSN= 5/6" Satin Nickel Trim Ring RL56TRMTBZ= 5/6" Tuscan Bronze Trim Ring RL56TRMWH= 5/6" White Paintable Trim Ring RL56TRMWH= 5/6" White Paintable Trim Ring RL56TRMWH= 5/6" White Paintable Trim Ring RL56TRMWH= 5/6" White BlackTrim Ring OT400P= Oversize Flat White Metal Trim Ring 6" l.D. x 9-1/4" O.D. (ring slips behind RL56 ring, in stepped configuration) OT403P= Oversize White Plastic Trim Ring 6" l.D. x 9-1/4" O.D. (ring slips behind RL56 ring, in stepped configuration) TRM690WH= Oversize Matte White Metal Trim Ring. Designed for RL560 ring to inset into oversize ring for an even (non-stepped) trim surface HE26LED= Replacement screw base adapter (one included with unit)

#### **Housing Compatibility**

Compatible Halo LED Housings with LED luminaire connector (high-efficacy compliant)			
Halo LED 5-inch H550ICAT= 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing H550RICAT= 5" LED, Insulated Ceiling, Air-Tite, Remodel Housing E550ICAT= 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing E550RICAT= 5" LED, Insulated Ceiling, Air-Tite, Remodel Housing	Halo LED 6-inch H750ICAT= 6" LED, Insulated Ceiling, Air-Tite, New Construction Housing H750RICAT= 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing H750T= 6" LED, Non-IC, Air-Tite, New Construction Housing H750TCP= 6" LED, Non-IC, New Construction/Remodel Chicago Plenum Housing H750INTD010= 6" LED, Non-IC, New Construction/Remodel Chicago Plenum Housing H750ICAT= 6" LED, Shallow, Insulated Ceiling, Air-Tite, New Construction (use with 691X, 694X, 696X trims only) H2750RICAT= 6" LED, Insulated Ceiling, Air-Tite, New Construction Housing E750ICAT= 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing		

## **Housing Compatibility**


Halo LED Retrofit	Enclosures
Halo LED retrofit ML7BRXFK= 6" Retrofit Enclosure, Non-IC, BX Whip ML7E26RFK= 6" Retrofit Enclosure, Non-IC, E26 Screw base Interface	


#### **Housing Compatibility**

nousi	ng Compatibility
Compatible Halo Incan	descent E26 Screwbase Housings
Halo Standard Housings 5-inch	H7ICTNB= 6" Insulated Ceiling, New Construction Housing, No Socket Bracket
H5ICAT= 5" Insulated Ceiling, Air-Tite New Construction Housing	H7T= 6" Non-IC, New Construction Housing
H5RICAT= 5" Insulated Ceiling, Air-Tite Remodel Housing	H7RT= 6" Non-IC, Remodel Housing
H5ICATNB= 5" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket	H7TNB= 6" Non-IC, New Construction Housing, No Socket Bracket
H5T= 5" Non-IC, New Construction Housing	H7TCP= 6" Non-IC, Chicago Plenum, New Construction/Remodel Housing
H5RT= 5" Non-IC, Remodel Housing	H7UICAT= 6" Insulated Ceiling, Universal, Air-Tite, New Construction Housing
H25ICAT = 5" Shallow, Insulated Ceiling, Air-Tite New Construction	H27ICAT = 6" Shallow, Insulated Ceiling, Air-Tite New Construction
H25ICATNB = 5" Shallow, Insulated Ceiling, Air-Tite New Construction, No Socket Bracket	H27RICAT = 6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing
H5TNB= 5" Non-IC, New Construction Housing, No Socket Bracket	H27T= 6" Shallow, Non-IC, New Construction Housing
ESICAT = 5" Insulated Ceiling, Air-Tite New Construction Housing	H27RT = 6" Shallow, Non-IC, Remodel Housing
E5RICAT = 5" Insulated Ceiling, Air-Tite Remodel Housing	E27ICAT= 6" Shallow, Insulated Ceiling, Air-Tite New Construction
ESICATNB= 5" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket	E27RICAT= 6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing
E5TAT= 5" Non-IC, New Construction Housing	E27TAT = 6" Shallow, Non-IC, New Construction Housing
E5RTAT = 5" Non-IC, Remodel Housing	E27RTAT = 6" Shallow, Non-IC, Remodel Housing
E5TATNB= 5" Non-IC, New Construction Housing, No Socket Bracket	ETICAT = 6" Insulated Ceiling, Air-Tite New Construction Housing
	E7RICAT= 6" Insulated Ceiling, Air-Tite Remodel Housing
Halo Standard Housings 6-inch	E7ICATNB= 6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket
H7ICAT = 6" Insulated Ceiling, Air-Tite New Construction Housing	E7TAT= 6" Non-IC, New Construction Housing
H7RICAT= 6" Insulated Ceiling, Air-Tite Remodel Housing	E7RTAT = 6" Non-IC, Remodel Housing
H7ICT= 6" Insulated Ceiling, New Construction Housing	E7TATNB= 6" Non-IC, New Construction Housing, No Socket Bracket
H7RICT= 6" Insulated Ceiling, Remodel Housing	
H7ICATNB= 6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket	



# **Designer Trim Dimensions**





# **Energy Data**

RL56 Series (Values at non-dimming line voltage)
Minimum Starting Temp: -30°C (-22°F)
EMI/RFI: FCCTitle 47 CFR, Part 15, Class B (Consumer)
Sound Rating: Class A
Input Voltage: 120V
Power Factor: >0.90
Input Frequency: 60Hz
THD: <20%
Input Power: 7.6W – RL560WH6827 7.3W – RL560WH6830, RL560WH6835, RL560WH6840 9.7W – RL560WH6927 8.7W – RL560WH6930, RL560WH6940 9.0W – RL560WH6935
Input Current: 0.15A
Maximum IC (Insulated Ceiling) Ambient Continuous Operating Temperature: 25°C (77°F)
Maximum Non-IC Ambient Continuous Operating Temperature 40°C (104°F)

# **Product and Photometric Data**

## **RL56 - 600 Series**

Cat No.	CRI	ССТ	Lumens	Power (W)	LPW
RL560WH6927	92	2700	630	8.7	72
RL560WH6930	91	3000	645	8.8	73
RL560WH6935	92	3500	650	8.9	73
RL560WH6940	92	4000	690	9.2	75
RL560WH6950	90	5000	715	8.9	80

## **RL56-600 Series Photometric\***

RL560WH6930			
Luminai	645		
Input	8.8		
LER (	73.3		
	0-180	1.14	
Spacing Criteria	90-270	1.14	
	Diagonal	1.22	
Beam angl	87.8		
Field angle	139		
Zonal lumen	Lumens	% Lumens	
0-30	240	37.2	
		37.2 58.2	
0-30	240		
0-30 0-40	240 375	58.2	

 $<sup>\</sup>ensuremath{^{\star}}$  Tested in accordance with IES LM63. Field results may vary.



HALO RL56 LED 600 Series

# **Product Specifications**

#### Mechanical Module - Trim

- Module construction includes LED, heat sink, reflector, lens, baffle and trim ring
- · Regressed baffle
- Heat sink designed to conduct heat away from the LED keeping the junction temperatures below specified maximums, even when installed in insulated ceiling environments. L70 at 50,000 hours.
- · Designer trim finish options (sold separately)
  - · White (Paintable) Trim Ring
  - · Satin Nickel Trim Ring
  - · Tuscan Bronze Trim Ring

#### Lens

- · Regressed lens
- · Impact-resistant polycarbonate
- · Convex form for lamp-like appearance
- · Diffusing for even illumination

#### Mounting

- Integral torsion springs and Push-N-Twist clips offer two mounting options
  - Torsion springs are pre-installed and adjust to fit 5" or 6" compatible housings
  - Push-N-Twist universal installation clips are preinstalled and designed to fit 5" or 6" compatible housings

#### **Housing Compatibility**

See Housing Compatibility

#### LED

- · Color Temperature (CCT)† Options:
  - · 90 CRI: 2700K, 3000K, 3500K, 4000K, and 5000K
- Can be used to comply with California Title 24
  High Efficacy requirements. Certified to California
  Appliance Efficiency Database under JA8.

## **LED Chromaticity**

- A tight chromaticity specification ensures LED color uniformity, sustainable Color Rendering Index (CRI) and Correlated Color Temperature (CCT) over the useful life of the LED
- LED chromaticity of 3 SDCM exceeds ENERGY STAR® color standards per ANSI C78.377-2008
- High color performance with R9 greater than 50
- Every Halo LED is quality tested, measured, and serialized in a permanent record to register lumens, wattage, CRI and CCT
- Halo LED serialized testing and measurement ensures color and lumen consistency on a
- per-unit basis, and validates long-term product consistency over time

## **Electrical**

#### **Power Connections**

- LED connector is a non-screw base luminaire disconnect offering easy installation with the matching Halo 5" and 6" LED housings
- · LED Connector meets California Title-24 high

- efficacy luminaire requirement for a non-screw base socket, and where required to qualify as a high efficacy luminaire
- The included E26 medium screw-base Edison adapter provides easy retrofit of incandescent housings (see Housing Compatibility)

#### **Ground Connection**

- Separate grounding cable included
- · on the module for attachment to the
- · housing during installation.

#### **LED Driver**

- With the latest "driver-on-board" electronic technology, the driver is integrated in the module.
- 120V 50/60 Hz constant current dimmable driver provides high-efficiency operation
- Driver meets FCC 47CFR Part 15 EMI/RFI consumer limits for use in residential and commercial installations
- Driver features high power factor and low THD and has integral thermal protection in the event of over temperature or internal failure
- If dimming is not required the fixture can be operated from a standard wall switch

#### Dimmin

- Designed for continuous dimming capability to nominally 5% with many 120V Leading Edge (LE) and Trailing Edge (TE) Phase Control dimmers. (Dimmers with low end trim adjustment offer greater assurance of achieving 5% level.)
- Consult dimmer manufacturer for compatibility and conditions of use Note: some dimmers require a neutral in the wallbox.

#### Warranty

Eaton provides a five year limited warranty on RL56 LFD

#### **Compliance Labels**

- UL Certified 1598 Luminaire with Halo housings and others – see Housing Compatibility
- · UL Certified for Damp Location
- · IP56 Ingress Protection rated
- May be installed in housings in direct contact with insulation\*\* and combustible material

#### Compliance


- Airtight certified per ASTM E283 (not exceeding 2.0 CFM under 75 Pascals pressure difference)
- 90 CRI: Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Title 20 Appliance Efficiency Database.\*
- Can be used for International Energy Conservation Code (IECC) high efficiency luminaire compliance.
- Suitable for use in closets. Compliant with NFPA 70, NEC Sec. 410.16 (A)(1) and 410.
   16 (C)(3).
- ENERGY STAR® Certified luminaire consult ENERGY STAR® Certified Product List\*
- EMI/RFI per FCC 47CFR Part 15 Class B Consumer limits, suitable for use in residential and commercial installations
- · Contains no mercury or lead and RoHS compliant.
- · Photometric testing in accordance with IES LM-79
- Lumen maintenance projections in accordance with IES LM-80 and TM-21



# **Lighting Facts**

#### RL560WH6927

2700K Source



#### RL560WH6930

3000K Source



#### **RL560WH6935** 3500K Source

# Light Output (Lumens) 650 Watts 8,9 Lumens per Watt (Efficacy) 73.03 Color Accuracy Color Rendering Index (CRI) 92 Light Color Rendering Index (CRI) 92 Light Color Rendering Index (CRI) 92 Light Color Rendering Index (CRI) 8500 (Bright White) 6500K All media are securing in IEDM LIGHT 2000 (Approach Maler for the Televisia and Protections Televis God Color Light (Light Light Color for the CRI) 8500 (Bright White) 8500K All media are securing in IEDM LIGHT 2000 (Approach Maler for the Televisia and Protections Televisia (Bright Color for the CRI) 8500K

## RL560WH6940

4000K Source



## RL560WH6950

5000K Source

