



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RM4 Relay Module

BRK Brands/Ademco/First Alert

Catalog Number	RM4
Manufacturer	BRK Brands/Ademco/First Alert
Description	Relay Module For Smoke and "Smart Interconnect" CO Alarms
Weight per unit	0.2500 (lbs/each)
Product Category	In Relays & Accessories

Features

amperage rating	0.02 amps (standby/alarm)
Contact Configuration	Form C normally open or normally closed
Contact Rating	Maximum 120V AC, 15 amp 1/3 horsepower motor, Minimum 30V, DC 15 amp

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	3.5" L x 1.5" H; 2.2 ozs.
------	---------------------------

Descriptions

Description	RELAY MODULE
extra long description	BRK RM4 120V AC Smart Relay
Features	Relay Module
Long Description	Relay Module for Smoke and "Smart Interconnect" CO Alarms
Product Type	120V Ac Smart Relay
Special Features	Interconnects Up to 18 units of First Alert or BRK Smoke, CO and Heat Alarms. Maximum of 12 smoke alarms. See user's manual for details.

Manufacturer Information

Brand	BRK
GTIN	00029054000576
UPC	029054000576

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	BRK Alarm Relay

Packaging

Carton	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	This accessory relay is designed to activate auxiliary devices such as bells, lights and door closers. The RM4 Relay is intended for use with BRK and First Alert Smoke, Heat, and Carbon Monoxide Alarms.
Enclosure	Shrink wrapped heat resistant material
environmental conditions	10 percent to 90 percent relative humidity (RH)
Frequency Rating	60
Mounting	Mounts Inside Junction Box
Operating Temperature	40 Degree F (4 Degree C) to 100 Degree F (38 Degree C)
standard	UL217, UL2034