



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RMJS16RDVB Relay Module

Lutron

Catalog Number	RMJS16RDVB
Manufacturer	Lutron
Description	Powpak Relay Module With Softswitch, 16A General Purpose Switch, 120/277V, Vive Enabled
Weight per unit	0.3100 (lbs/each)
Product Category	General Purpose Power Relays

Features

amperage rating	16 A/.5 HP@120/1.5 HP@277 V
connection	Wire Leads
Contact Configuration	N-O
Contact Rating	16 A/.5 HP@120/1.5 HP@277 V
insulation	Plastic
Material	Plastic/Metal
Voltage Rating	120 to 277

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	3.94 x 2.82
------	-------------

Descriptions

Description	RELAY MODULE
extra long description	LUT RMJS-16R-DV-B RELAY MODULE, VIV
Long Description	PowPak relay module with Softswitch, 16A general purpose switch, 120/277V, Vive enabled
Product Type	Relay Module, Vive Enabled
Special Features	Radio frequency (RF) device that uses Lutron patented SoftSwitch technology to control general-purpose loads based on input from Pico controls and Radio Powr Savr occupancy and daylight sensors An optional, low-voltage dry contact closure output is available to communicate occupancy status to 3rd-party systems such as HVAC controllers (RMJ-, URMJ-, RMQ-, RMM-, RMP-models only). Communication with RF input devices is accomplished using Lutron Clear Connect RF Technology. Softswitch Lutron patented technolo

Manufacturer Information

Brand	Lutron
GTIN	00784276150460
Manufacturers Part Number	RMJS-16R-DV-B
UPC	784276150460



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	GENERAL PURPOSE RELAYS
Type	Relay module with Softswitch

Packaging

Carton	1
Weight Per each	0.31

Uses, Certifications, and Standards

Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	JUNCTION BOX
Operating Temperature	32 to 104
standard	UL, FCC, CSA, IC, COFETEL, NOM