



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SVX010A24A1B2 SVX9000 10HP 480V NEMA12 W/BR Chop Alfa PNL W/Conf *Eaton Corp*

Catalog Number	SVX010A24A1B2
Manufacturer	Eaton Corp
Description	Eaton SVX Adjustable Frequency Drive, 10HP, Nema Type 12/IP54, 480V, FR5, Three-Phase, Emc H, Standard Software, A/N Keypad, Internal Brake Chopper, Varnished Boards
Weight per unit	24.0 (lbs/each)
Product Category	Ac Drives

Features

dimensions	8.4000 IN X 5.6000 IN X 16.5000 IN
keypad	Alphanumeric

Descriptions

Description	SVX9000 10HP 480V NEMA12 W/BR CHOP ALFA PNL W/CONF
extra long description	ETN SVX010A2-4A1B2 SVX9000 10HP 480
Features	Demand more accurate speed control. Eaton's SVX series of variable frequency drives offer sensorless vector control technology coupled with an adaptive motor model and sophisticated ASIC circuit features. This technology allows for steady speed error, fast torque rise time, high immunity to resonance vibrations and high starting torque and current. The SVX9000 is suitable for multiple motor drive systems and high-speed applications.
Long Description	Eaton SVX adjustable frequency drive, 10HP, NEMA Type 12/IP54, 480V, FR5, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Varnished Boards
Product Type	SVX9000 10HP 480V N12 BC W/Conf Coat

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116129614
Manufacturers Part Number	SVX010A2-4A1B2
UPC	782116129614

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Adjustable frequency drive

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	24



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

IEC 61800-2,UL 508C,EN 61800-3 Level H,Contact Manufacturer