

# Eaton SVX010A2-4A1B2

Catalog Number: SVX010A2-4A1B2

Eaton SVX adjustable frequency drive, 10HP, NEMA Type 12/IP54, 480V, FR5, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Varnished Boards

Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX010A2-4A1B2
<b>UPC</b>	<b>Product Length/Depth</b>
782116129614	8.4 in
<b>Product Height</b>	<b>Product Width</b>
16.5 in	5.6 in
<b>Product Weight</b>	<b>Warranty</b>
17.9 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	UL 508C EN 61800-3 Level H IEC 61800-2



## defaultTaxonomyAttributeLabel

### Brake chopper

Brake chopper

### Modification

Varnished Boards

### Horsepower

10 hp

### Frame size

5

### Keypad

Alphanumeric

### Input

EMC H

Three-phase

### Rating

NEMA 12, IP54

### Software

Standard

## Resources

### Application notes

SPI - Variable frequency drives with a common DC bus

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

### Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

### Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Range Catalog Drives Engineering

Product Datasheet - SVX010A2-4A1B2

### Drawings

SVX and SPX Series FR4-FR11 PDF Open Drawings

### Installation instructions

9000X AFD User Manual

### Specifications and datasheets

Eaton Specification Sheet - SVX010A2-4A1B2



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia