



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S10N04P26P .25KVA Buck Boost Transformer 1PH 120X240-12/24V

Eaton Corp

Catalog Number	S10N04P26P
Manufacturer	Eaton Corp
Description	Eaton General-Purpose Encapsulated Transformer, Ep, Single-Phase, PV- 120 X 240V, Taps- None, SV- 12/24V, 115°C, .250 Kva, Al Windings, Frame- 57P, Indoor-Outdoor.
Weight per unit	30.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

connection	509A
design	EP
dimensions	5.1800 IN X 4.4500 IN X 9.3400 IN
frame	57P
Number of Phases	Single-phase
Primary Voltage	120 V, 240 V
Secondary Voltage	12/24 V

Descriptions

Description	.25KVA BUCK BOOST TRANSFORMER 1PH 120X240-12/24V
extra long description	ETN S10N04P26P .25KVA BUCK BOOST TX
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV- 120 X 240V, Taps- None, SV- 12/24V, 115°C, .250 kVA, Al windings, Frame- 57P, Indoor-Outdoor.
Product Type	.25KVA Buck Boost TX 1PH 120X240-12/24V

Manufacturer Information

Brand	Eaton
GTIN	00786680073571
Manufacturers Part Number	S10N04P26P
UPC	786680073571



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....BUCK & BOOST TRANSFORMERS

Type.....Encapsulated transformer

Packaging

Carton.....1

Weight Per each.....30

Uses, Certifications, and Standards

Application.....Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Frequency Rating.....60 Hz

standard.....UL Listed

Temperature Rating.....115 °C rise