

Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
UPC	Product Length/Depth
782116011599	13.5 in
Product Height	Product Width
30.1 in	11.5 in
Product Weight	Warranty
127 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Modification

Standard boards

Horsepower

125 hp

Frame size

8

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Resources

Application notes

SPI - Variable frequency drives with a common DC bus

Connecting drives to generator supplies

Electromagnetic compatibility (EMC)

Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - SVX125A1-4A1N1

Product Range Catalog Drives Engineering

Drawings

SVX_(FR8) 2D Drawing Xchange

SVX and SPX Series FR4-FR11 PDF Open Drawings

SVX_(FR8) 3D Model Xchange

SVX_(FR8) 2D PDF

SVX_(FR8) 3D Inventor

SVX_(FR8) AutoCAD 2D Footprint (mm)

SVX_(FR8) AutoCAD 2D Footprint

Installation instructions

9000X AFD User Manual

Specifications and datasheets

Eaton Specification Sheet - SVX125A1-4A1N1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia