



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S20N11P76P .75KVA Type Ep Transformer 1PH 240X480-120/240V

Eaton Corp

Catalog Number	S20N11P76P
Manufacturer	Eaton Corp
Description	Eaton General-Purpose Encapsulated Transformer, Ep, Single-Phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, .75 Kva, Alum Windings, Frame: 58AP, Indoor-Outdoor
Weight per unit	22.3 (lbs/each)
Product Category	2011202162409

Features

design	EP
dimensions	5.9900 IN X 4.9900 IN X 11.6800 IN
kva rating	0.75 kVA
Number of Phases	Single-phase
Tap Size	NONE

Descriptions

Description	.75KVA TYPE EP TRANSFORMER 1PH 240X480-120/240V
extra long description	ETN S20N11P76P 0.75 kVA Encapsulate
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, .75 kVA, Alum windings, Frame: 58AP, Indoor-Outdoor
Product Type	0.75 Kva Encapsulated XFMR 1PH

Manufacturer Information

Brand	Eaton
GTIN	00786680233852
Manufacturers Part Number	S20N11P76P
UPC	786680233852

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Encapsulated transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	22.26

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
Frequency Rating	60 Hz
standard	UL Listed, Not Applicable
Temperature Rating	115 °C rise