



120 X 240 - 12/24  
120 X 240 Primary Volts - 12/24 Secondary Volts - 1Ø  
Buck-Boost Transformer - Single Phase

1082



Catalog #: T181051

#### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 47

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA:	500
kVA:	-
Primary Voltage:	120 X 240
Secondary Voltage:	12/24
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	9.06 (23.0)
Width (In./cm):	4.37 (11.1)
Depth (In./cm):	4.20 (10.7)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

#### PACKAGING

Ship Weight (Lbs/Kg):	15 (6.8)
-----------------------	----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)



120 X 240 - 12/24  
120 X 240 Primary Volts - 12/24 Secondary Volts - 1Ø  
Buck-Boost Transformer - Single Phase

1082



Catalog #: T181051

#### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 47

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA:	500
kVA:	-
Primary Voltage:	120 X 240
Secondary Voltage:	12/24
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	9.06 (23.0)
Width (In./cm):	4.37 (11.1)
Depth (In./cm):	4.20 (10.7)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

#### PACKAGING

Ship Weight (Lbs/Kg):	15 (6.8)
-----------------------	----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)