

Specifications



Eaton S20N11S05N

Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 240 x 480v, taps: none, sv: 120/240v, 115°C, 5 kva, al windings, frame: 177, indoor-outdoor

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20N11S05N
UPC	786680102974
PRODUCT LENGTH/DEPTH	9.89 in
PRODUCT HEIGHT	16 in
PRODUCT WIDTH	10.38 in
PRODUCT WEIGHT	126 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Model N

Physical Attributes	
COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	177
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Performance Ratings	
FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	5 kVA

Resources	
CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S20N11S05N

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

