



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S20N11S25N 25KVA Type Ep Transformer 1PH 240X480V-120/240V

Eaton Corp

Catalog Number	S20N11S25N
Manufacturer	Eaton Corp
Description	Dry Type Transformer, 240 X 480 V, 120/240 V, 25 K Va Va Rating, Encapsulated Transformer, 14.12 In Overall Length, 25 In Overall Width, 20.2 In Overall Height, 60 HZ, 115 °C Temperature Rise Rating, 385 LB
Weight per unit	385.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

design	EP
dimensions	20.0000 IN X 25.0000 IN X 20.2000 IN
kva rating	25 kVA
Number of Phases	Single-phase
Tap Size	NONE

Descriptions

Description	25KVA TYPE EP TRANSFORMER 1PH 240X480V-120/240V
extra long description	ETN S20N11S25N 25KVA Type EP XFMR 1

Manufacturer Information

GTIN	00786680108839
UPC	786680108839

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Encapsulated transformer

Packaging

Carton	1
Weight Per each	385

Uses, Certifications, and Standards

Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	115 °C rise