



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T2535173S 15KVA 1PH 240/480 Transformer *Acme Electric*

Catalog Number	T2535173S
Manufacturer	Acme Electric
Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 15kva
Weight per unit	170.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

Fuse Rating	Primary: 80 AMP For 240 V, 40 AMP For 480 V, Secondary: 175 AMP For 120 V
pallet quantity	6
Primary Voltage	240 x 480 V
product category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V

Dimensions and Weight

Height	16.94
Length	11.59
Width	14.12

Descriptions

Construction	ENCAPSULATED
Description	15KVA 1PH 240/480 TRANSFORMER
extra long description	ACME T2535173S TFMR 1PH 15KVA 240X4
Long Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 15kVA
Product Type	Dry Type Distribution Transformer
Special Features	Encapsulated core and coil; Shielded for cleaner power; Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air, UL type 3R enclosure for indoor or outdoor service, encapsulation eliminates corrosion and insulation deterioration; Quiet operation with sound levels well below NEMA standards; 10-year limited warranty

Manufacturer Information

Brand	ACME ELECTRIC
GTIN	00047503734155
Manufacturers Part Number	T2535173S
UPC	047503734155



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Distribution Transformer

Packaging

Carton	1
Weight Per each	170

Uses, Certifications, and Standards

Enclosure	NEMA 3R Steel
Frequency Rating	60
Mounting	WALL
standard	UL 506, UL File Number E79947V1, UL Control Number 50B8, UL Insulation Number H3221, CSA Certified, OSHA Compliant, ANSI, IEEE
Temperature Rating	115 DEG C Rise