

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

SATCO S23151

27W/LED/CCT/100-277V/EX39

Notes

[www] 04-25-2022 02:43:09

General

Status	Active
Watts	27W/22W/18W
HID Equivalent	125W/100W/75W
Volts	100V-277V
Base	Extended Mogul
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
CRI	80
Lumens	3780L/3080L/2520L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Ballasting Requirements	Ballast Bypass

Electrical

Operating Frequency	50-60 Hz
Dimming Note	Dimmable only via the wattage/lumen selectable dial included on lamp
Power Factor	>0.9
Burning Position	Base Up, Base Down, or Horizontal
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical

MOL	7.48
MOD	2.32
Lens Material	Plastic
Housing Color	Dark Gray
Weight (lb.)	0.75

Additional Information

Additional Info	Power selectable
IP Rating	IP64
Warranty	5 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus - Classified; cULus - Certified; cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-HJ4T6Y
CA T20 / T24 Rationale	Exempt - Base Not Regulated
RoHS Compliant	Yes
FCC Compliant	Yes

