

Calbrite™

Stainless Steel Conduit Systems

Stainless Steel C Condulet

Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Designed for use with stainless threaded conduit
- Solid stainless construction permits easy installation using ordinary hand tools
- The flat back design allows extra wiring capacity
- No package qty. required
- Cover & Gasket included
- Form 8 Style



Material:

Material: Body CF8M- 316SS

Gasket - Neoprene

Cover & Screws: 316SS

Applications:


To connect and change direction of conduit runs

Can be used as pulling fittings

Accessible wiring chamber provides a spacious location to make splices

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments



Size	Part Number	A	B	C	a	Cubic Inches	Weight (ea) per lb.
1/2"	S60500CE00	5.690"	1.330"	1.720"	4.320"	5"	1.15
3/4"	S60700CE00	6.280"	1.560"	2.020"	4.950"	9"	1.64
1"	S61000CE00	7.330"	1.740"	2.020"	5.640"	13"	2.19
1-1/4"	S61200CE00	8.520"	2.120"	2.630"	6.550"	24"	3.19
1-1/2"	S61500CE00	10.50"	2.530"	2.740"	7.810"	35"	4.63
2"	S62000CE00	12.30"	3.480"	3.550"	10.00"	77"	8.66

*All dimensions are for informational purposes only *Tolerances +/- 5%*

Calbrite™

Stainless Steel Conduit Systems

Stainless Steel C Condulet

Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Designed for use with stainless threaded conduit
- Solid stainless construction permits easy installation using ordinary hand tools
- The flat back design allows extra wiring capacity
- No package qty. required
- Cover & Gasket included
- Form 8 Style



Material:

Material: Body CF8M- 316SS

Gasket - Neoprene

Cover & Screws: 316SS

Applications:


To connect and change direction of conduit runs

Can be used as pulling fittings

Accessible wiring chamber provides a spacious location to make splices

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments



Size	Part Number	A	B	C	a	Cubic Inches	Weight (ea) per lb.
1/2"	S60500CE00	5.690"	1.330"	1.720"	4.320"	5"	1.15
3/4"	S60700CE00	6.280"	1.560"	2.020"	4.950"	9"	1.64
1"	S61000CE00	7.330"	1.740"	2.020"	5.640"	13"	2.19
1-1/4"	S61200CE00	8.520"	2.120"	2.630"	6.550"	24"	3.19
1-1/2"	S61500CE00	10.50"	2.530"	2.740"	7.810"	35"	4.63
2"	S62000CE00	12.30"	3.480"	3.550"	10.00"	77"	8.66

All dimensions are for informational purposes only *Tolerances +/- 5%