



S840C0 7.87" 40LB BLK Nylon CBL Tie

Panduit Corporation

Catalog Number	S840C0
Manufacturer	Panduit Corporation
Description	The S8-40-C0 Stronghold Cable Ties Offers Contractors An Economical Cable Tie Option For Commercial Construction and General-Purpose Applications. Intermediate, 7.87" (200MM) Length and Are AH-2 Plenum Rated. For Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 100.
Weight per unit	0.1950 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	40

Dimensions and Weight

Length	7.9
Thickness	0.05

Descriptions

Description	7.87" 40LB BLK NYLON CBL TIE
extra long description	PAN S8-40-C0 StrongHold™ S8-40-C0 C
Long Description	The S8-40-C0 StrongHold Cable Ties offers contractors an economical cable tie option for commercial construction and general-purpose applications. Intermediate, 7.87" (200mm) length and are AH-2 Plenum rated. For outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 100.
Product Type	Stronghold™ S8-40-C0 Cable Tie, Black, Pa 6.6, 40LB Min Loop
Special Features	Plenum

Manufacturer Information

Brand	Panduit®
GTIN	00613056257948
Manufacturers Part Number	S8-40-C0
UPC	613056257948

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	1000
Weight Per each	0.195

Uses, Certifications, and Standards

standard	UL 62275 Compliant (Type 2, 21), RoHS Compliant
----------	---