



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

TFFN18STRD500 TFFN 18 STR Red 500 *Southwire Company*



Catalog Number	TFFN18STRD500
Manufacturer	Southwire Company
Description	Copper Fixture Wire, 6 A (TFFN);7 A (MTW), 600 V, 16 Strands, 1 Conductor, #18 Awg Conductor Size, Red, 500 FT Overall Length, 85 Mil Outside Diameter, 15 Mil Insulation Thickness, +90 °C Operating Temperature, 0.0071 LB/FT
Weight per unit	0.0071 (lbs/ft)
Product Category	TFFN-STR (Stranded)

Features

Stranding	16 STRANDS
-----------	------------

Material, Color, and Finish

Jacket Color	RED
--------------	-----

Dimensions and Weight

Length	500 FT
Length in ft	500 W
Outer Diameter	85 MIL

Descriptions

Commodity Description	COPPER BUILDING WIRE-TFFN-STR
Description	TFFN 18 STR RED 500

Manufacturer Information

Brand	Copper
GTIN	00032886226205
UPC	032886226205

Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
Type	TFFN, MTW/AWM

Availability

minimum qty	500
-------------	-----

Packaging

Carton	500
Package	2000
Weight Per foot	0.0071



ELLIOTT ELECTRIC SUPPLY


We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Approval	UL 66
Temperature Rating	90 TO 105 DEG C

TFFN/TFN/TEWN



600 Volt

Copper Conductor

Thermoplastic Insulation/Nylon Sheath

Heat, Moisture, Oil and Gasoline Resistant¹

Rated MTW and 105°C AWM

TFN Also Available

APPLICATIONS Suitable for use as follows:

- Southwire Type TFFN or MTW or AWM may be used as fixture wire, machine tool wiring, or appliance wiring material as specified in the National Electrical Code^{®2}
- When used as Type TFFN, conductor is suitable for use at temperatures not to exceed 90°C
- When used as Type MTW, conductor is suitable for use in wet locations or when exposed to oil or coolant at temperatures not to exceed 60°C or dry locations at temperatures not to exceed 90°C (with ampacity limited to that for 75°C conductor temperature per NFPA 79)
- Conductor temperatures not to exceed 105°C in dry locations when rated AWM and used as appliance wiring material
- Voltage for all applications is 600 volts

STANDARDS & REFERENCES

Southwire Type TFFN or MTW or AWM meets or exceeds UL Standard 66 and requirements of the National Electrical Code.[®] RoHS Compliant.

CONSTRUCTION

- Southwire Type TFFN or MTW or AWM copper conductors are annealed (soft) copper, insulated with a tough, heat and moisture resistant polyvinyl chloride (PVC), over which a nylon (polyamide) jacket is applied
- Available in black, white, red, blue, green, yellow, orange, brown, purple, grey and pink; some colors standard, some subject to economic order quantity

SPECIFICATIONS

- **TFFN:**
Conductors shall be UL-listed Type TFFN or MTW or AWM gasoline and oil resistant II, suitable for operation at 600 volts as specified in the National Electrical Code.[®] Conductors shall be annealed copper, insulated with high-heat and moisture resistant PVC, jacketed with abrasion, moisture, gasoline and oil resistant nylon, as manufactured by Southwire Company or approved equal.
- **TFN:**
Southwire Type TFN conductors may be used as fixture wire and as permitted for fire protective signal circuits as specified in the National Electrical Code.[®] at conductor temperatures not to exceed 90°C or 105°C when used as AWM. Voltage rating for all applications is 600 volts.


* rated -2 for 8 AWG and larger only

¹ Oil and gasoline resistant II as defined by Underwriters Laboratories

² 2005 Edition



green Spec[®]
RoHS Compliant
2002/95/EC



HVAC

TFN/TFN/TEWN

WEIGHTS, MEASUREMENTS, AND PACKAGING

SIZE (AWG)	NUMBER OF STRANDS	VINYL THICKNESS (mils)	NYLON JACKET (mils)	NOMINAL O.D. (mils)	APPROX. NET WEIGHT PER (lbs/1000 ft)	ALLOWABLE AMPACITIES**		STANDARD PACKAGE*
						TFN	MTW	
18	16	15	4	85	7	6	7	DNFP
16	26	15	4	99	11	8	10	DNFP

*Four 500' spools per carton.
 **Ampacities shown are for general use as specified by the National Electrical Code®, 2005 Edition. TFN as specified by section 402.5 and MTW as specified by NFPA 79.

STANDARD PACKAGE CODES
 F – 500 ft. spool
 N – 2000 ft. carton
 D – 2500 ft. spool
 P – Drum

WEIGHTS, MEASUREMENTS, AND PACKAGING

SIZE (AWG)	NUMBER OF STRANDS	VINYL THICKNESS (mils)	NYLON JACKET (mils)	NOMINAL O.D. (mils)	APPROX. NET WEIGHT PER (lbs/1000 ft)	ALLOWABLE AMPACITIES**		STANDARD PACKAGE TFN*
						TFN	MTW	
18	1	15	4	78	7	6		DNFP
18	7	15	4	82	7	6		DNFP
16	1	15	4	89	10	8		DNFP
16	7	15	4	94	11	8		DNFP

*Four 500' spools per carton.
 **Ampacities shown are for general use as specified by the National Electrical Code®, 2005 Edition. TFN as specified by section 402.5.

STANDARD PACKAGE CODES
 F – 500 ft. spool
 N – 2000 ft. carton
 D – 2500 ft. spool
 P – Drum