



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## SB1408S 14-8AWG STL Crimp Sleeve

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | SB1408S  |
| Manufacturer     | Nsi Industries   |
| Description      | The Easy-Twist SB1408S 50-Count Pack Of Steel Crimp Sleeve Wire Connectors Are Designed For Use On Wires In The 14-8 Awg Size Range. The Simple Brass-Plated Sleeve Design Forms Low-Resistance Connections In A Tight Space and Installs Using A Specialized Crimp Tool or Adjustable Pliers. Use Crimp Sleeves to Permanently Connect Wires In Grounding, Uninsulated or Small Motor Applications Where Vibration Resistance Is A Concern. |
| Weight per unit  | 0.5000 (lbs/each)  |
| Product Category | Small Terminals & Connectors   |

### Features

|                      |              |
|----------------------|--------------|
| Material             | Steel        |
| Number of Conductors | 1            |
| Poles                | 1            |
| Voltage Rating       | 600 V        |
| Warranty             | 1 YEAR       |
| Wire Size            | 14-8 AWG     |
| Wire Type            | CU Wire Only |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Steel |
| Finish | Steel |

### Dimensions and Weight

|      |                           |
|------|---------------------------|
| Size | L=.610 - W=.364 - ID=.263 |
|------|---------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 14-8AWG STL CRIMP SLEEVE  |
| extra long description | NSI SB1408S Crimp Sleeve 14-8 Steel   |
| Features               | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. The steel crimp sleeve wire connector provides a quick, economic and vibration-resistant way to form permanent connections in most applications. Simply twist your wires to form a connection, then slide the sleeve "sometimes called a ground cap" down to the twist and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these brass-plated steel cri |
| Long Description       | The Easy-Twist SB1408S 50-Count Pack of Steel Crimp Sleeve Wire Connectors are designed for use on wires in the 14-8 AWG size range. The simple brass-plated sleeve design forms low-resistance connections in a tight space and installs using a specialized crimp tool or adjustable pliers. Use crimp sleeves to permanently connect wires in grounding, uninsulated or small motor applications where vibration resistance is a concern.  |
| Product Type           | Crimp Sleeve 14-8 Steel, PK Of 50   |
| Special Features       | Steel Crimp Sleeves - 100 Pcs Blister   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Easy-Twist     |
| GTIN                      | 00662381402455 |
| Manufacturers Part Number | SB1408S        |
| UPC                       | 662381402455   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Crimp Sleeve Wire Connectors      |

## Packaging

|                    |     |
|--------------------|-----|
| Carton             | 1   |
| Weight Per package | 0.5 |

## Uses, Certifications, and Standards

|                          |               |
|--------------------------|---------------|
| Application              | Splicing Wire |
| environmental conditions | 105 C         |
| standard                 | UL 486C       |
| Temperature Rating       | 105 C         |