



TM CX8302 3" Cord Grips

Crouse-Hinds

Catalog Number	TM CX8302
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series TM CX Cable Gland, Metal-Cladcorrugated, Teck Armoured and Tray Cable, Armoured Barrier and Non-Armoured Barrier, Aluminum, Outer Sheath: 2.52-3.28", 3" NPT, Armor Range: 2.45-3.02"
Weight per unit	7.6 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Male NPT
dimensions	7.5000 IN X 4.8800 IN X 4.8800 IN
Material	Aluminum Body, Neoprene Seal

Dimensions and Weight

Size	3 in
------	------

Descriptions

Description	3" CORD GRIPS
extra long description	CRS-H TM CX8302 3 FT MC CAB ARMOR OD
Features	For use with metal-clad, non-armoured and tray cable, TM CX cable fittings are installed to provide a means for terminating cable at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution. They are used to form a mechanical watertight connection and to provide ground continuity of cable armour. Applied in Division 1 locations and when a seal is required.
Long Description	Eaton Crouse-Hinds series TM CX cable gland, Metal-cladcorrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 2.52-3.28", 3" NPT, Armor Range: 2.45-3.02"
Product Type	3 FT MC Cab Armor Od 2.45-3.02
Special Features	Armoured/Non-Armoured Barrier Gland

Manufacturer Information

Brand	Eaton
GTIN	00782274414744
Manufacturers Part Number	TM CX8302
UPC	782274414744

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell
88101-0000, NM Clovis
Phone: 575-742-2504
Fax: 575-742-2508

Packaging

Carton	1
Weight Per each	7.55

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	IP56, Class I Div 1 Group A B C D, Class II, Class III
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 60 Deg C