

Technical Specifications (continued)

Construction

Green Technology:

Mercury and UV free. RoHS-compliant components.

Finish:

Formulated for high durability and long-lasting color

Other

5 Yr Limited Warranty:

The RAB 5-year, limited warranty covers light output, driver performance and paint finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Equivalency :

Equivalent to 32W 4 Lamp T8 or 59W 2 Lamp T8

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Electrical

Driver:

Constant Current, Class 2, 120-277V, 50/60Hz, 120V: 0.89A, 208V: 0.52A, 240V: 0.45A, 277V: 0.38A


THD:

9.4% at 120V, 12.1% at 277V

Power Factor:

99.4% at 120V, 97.3% at 277V

Dimensions



Features

- Includes V hooks for chain mounting and brackets for surface mounting
- 6 ft, 5-wire cord included for easy installation
- Stainless steel fastening clips
- IP65 Rated
- 0-10V dimming
- 50,000-Hour LED lifespan
- 5-Year, Limited Warranty

Ordering Matrix

Family	Length	Wattage	Color Temp	Driver	Options
SEAL	8	100		/D10	
	4 = 4 ft 8 = 8 ft	50 = 50W 100 = 100W	Blank = 5000K (Cool) N = 4000K (Neutral)	/D10 = 0-10V Dimming 120-277V	Blank = No Option /LC = Lightcloud® Controller /LCS = Lightcloud® Sensor 120-277V ¹

¹ Suitable for damp locations only.